



# Sheet steel levelling feet, bolt-down

## Mounting instructions


### In a post with a blind hole



Using the flats on the thread, insert the stem into the blind hole and adjust to the required height




Tighten the lock nut (not supplied) and then secure the foot to the ground




Once levelled, tighten the nut to the base to secure the stem in its angular position


### Using mounting brackets



Adjust the height of the foot using a nut and counter-nut (not supplied)




Once at the required height, secure the foot to the ground




Once levelled, tighten the nut to the base to secure the stem in its angular position

# Stainless steel swivelling foot


## Mounting instructions



Grease the seal and thread with food-grade grease




Set the height of the foot by adjusting the screw (whilst not attached to the machine)




Adjust the sleeve in order to bring the upper seal into contact with the bottom of the machine




### Advice on cleaning




The thread must be completely covered by the sleeve



Rinse with water (Max. temperature 40°C)



Apply an alkaline detergent (Max. temperature 90°C) and leave to act for 10 min



Rinse with water at 8-12 bar (max. 100°C) using a jet inclined at 45° at a minimum distance of 300 mm to avoid damage to the seals