

Minimum double shear resistance (kN) according to ISO 8749

EP range - nickel stainless steel

Diameters Ø	0,8	1,0	1,2	1,5	2,0	2,5	3,0	3,5	4,0	5,0	6,0	8,0	10,0	12,0
Standard series ISO 8750	0,30	0,45	0,65	1,05	1,9	2,9	4,2	5,7	7,6	11,5	16,8	30	48	67

SRP range - stainless steel 304

Diameters Ø	1,5	2,0	2,5	3,0	4,0	5,0	6,0	8,0	10,0
Standard series ISO 8752	0,98	1,81	2,84	4,07	7,25	10,75	16,17	26,46	42,14

DH range - hardened steel

Diameters Ø	1,0	1,5	2,0	2,5	3,0	4,0	5,0	6,0	8,0	10,0	12,0	16,0	20,0
Standard series DIN 6325	1,5	3,4	5,5	8,0	13,0	22,0	31,0	53,0	88,0	132,0	210,0	350,0	485,0

DP range - stainless steel A2

Diameters Ø	1,0	1,5	2,0	2,5	3,0	4,0	5,0	6,0	8,0	10,0	12,0
Standard series ISO 2338	0,7	1,7	2,9	4,4	6,6	11,7	18,1	26,0	47,0	64,1	92,0