

Locking toggle clamps

Quick clamping - solid mounting

Durable and reliable: More reliable, more user-friendly and safer. These clamps are quick to use, reliable and accurate. The use of high quality materials ensures a long working life.


Advantages

- **Extremely tough** : All models will withstand 300,000 clamping cycles without problems
- **Durable**: high quality scratch resistant hinge pin
- **Extremely robust** : tCorrosion-resistant NITROX coating
- **Easy to use**: The fixed headed nut facilitates spindle adjustment
- **Reliable**: Constant level of force during both opening and closing
- **Ideal where space is restricted**: The slim design allows sufficient space for safe operation
- **Robust by design**: Thanks to use of U-shaped conical clamping arm
- **Safe to use**: No sharp edges prevent risk of anything getting trapped
- **Quick to put into operation**: Can be easily modified thanks to a wide range of accessories
- **Ergonomic design**: Easy to operate whilst wearing work gloves
- **Reflection free finish**: Suitable for use around lasers
- **Risk free use**: With increased space between clamping arm and handle avoids risks of squashing
- **Extremely adaptable**: Rectangular mounting holes allows installation on existing fixing points
- **Efficient clamping and locking**: The integrated design avoids any risks of squashing. Easy to use even whilst wearing gloves.

Locking mechanism - Principal of operation:



1. Locked in closed position. Redesigned handle ensures safe operation as the smooth contours avoid any risk of anything being trapped.



2. Inner locking mechanism with automatic safety catch. The lock is released by pulling the handle.



3. Locked in open position. Releasing the handle engages the locking mechanism.

