

Articulated coupling for actuator rod

CARv

With external connection thread

- Coupling with radial offset compensation for multiple applications
- Link between an actuator rod and a linear movement system
- Simple and solid two part coupling using a T shaped slot
- No manual adjustment required
- Materials:
 - Claw: Steel, tempered and phosphated
 - Connector: Steel, tempered and phosphated
 - Counter screw: Black steel (ISO 4035/8675)




Application

- A quick-fit coupling that can be linked to all commonly used pneumatic and hydraulic actuators via the connecting thread.

Info

- The coupling is not capable of transmitting any torque



DISCOUNTS

Qty	1+	5+	10+
Disc.	List -6%	On request	

Part number	ØD1	ØD2	L1	L2	L3	L4	L5	SW1	SW2	Max radial shift	Max load* (kN)	Weight (g)	Price each 1 to 4
CAR-M6-V	M6	21,0	37,5	11,0	14	9,0	18,0	19	10	0,6	2,5	44	39,15 €
CAR-M8-V	M8	26,0	45,0	13,5	17	11,5	22,5	24	13	0,7	4,5	86	41,22 €
CAR-M10-V	M10	30,0	56,2	16,0	20	16,0	29,0	27	17	0,7	6,5	147	48,56 €
CAR-M12-V	M12	32,5	66,7	21,0	25	17,0	34,0	30	19	0,8	10,0	208	54,88 €
CAR-M16-V	M16	39,0	83,0	25,0	30	23,0	42,0	36	24	1,0	18,0	383	66,70 €
CAR-M20-V	M20	44,0	93,5	29,0	35	23,5	45,5	41	30	1,0	30,0	571	80,75 €
CAR-M10F-V	M10x1,25	30,0	56,2	16,0	20	16,0	29,0	27	17	0,7	6,5	147	48,56 €
CAR-M12F-V	M12x1,25	32,5	66,7	21,0	25	17,0	34,0	30	19	0,8	10,0	207	54,88 €
CAR-M16F-V	M16x1,5	39,0	83,0	25,0	30	23,0	42,0	36	24	1,0	18,0	384	66,70 €
CAR-M20F-V	M20x1,5	44,0	93,5	29,0	35	23,5	45,5	41	30	1,0	30,0	576	80,75 €

*Permissible tensile and compression stress - Dimensions in mm