Stainless steel cam follower


Bearing diameters from 10 to 52mm


IKO

CFUUR/SS

- ***Axle mounted cam followers***
- *With synthetic rubber seals mounted in the external ring*
- *Easy fitted using an allen key*
- *For mounting holes from 3 to 20mm, tolerance H7*
- *Material – Stainless steel*







DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-20%	On request

Part number	Ø Min shoulder size (mm)	Max tightening torque (Nm)	Dynamic load C (N)	Static load base C (N)	max. load (N)	Max speed (1) (rpm)	g1 (mm)	g2 (mm)	r min. (mm)	Weight (g)
CF3UUR/SS	6,8	0,34	1200	813	384	50000	-	-	0,2	4,3
CF4UUR/SS	8,3	0,78	1650	1270	834	34000	-	-	0,3	7,4
CF5UUR/SS	9,3	1,60	1930	1730	1260	38000	-	-	0,3	10,3
CF6UUR/SS	11,0	2,70	2930	2920	1950	22000	-	-	-	18,5
CF8UUR/SS	13,0	6,50	3400	3790	3790	17000	-	-	-	28,5
CF10UUR/SS	16,0	13,80	4340	5510	5510	14000	-	-	-	45,0
CF12UUR/SS	21,0	21,90	6330	7830	7830	11000	4	3	-	95,0
CF16UUR/SS	26,0	58,50	9620	14700	14700	8500	4	3	-	170,0
CF18UUR/SS	29,0	86,20	14800	25200	25200	7000	6	3	1,0	250,0
CF20UUR/SS	34,0	119,0	20700	34600	34600	6500	6	4	1,0	460

Part number Crowned outer ring	Ød1 (h7)	ØD (h5)	C	ØG	G1	B	B1	B2	B3	C1	H	Stock*	Price each 1 to 5
CF3UUR/SS	3	10	7	M3 x 0,5	5,0	8,0	17,0	9,0	-	0,5	2	✔	70,94 €
CF4UUR/SS	4	12	8	M4 x 0,7	6,0	9,0	20,0	11,0	-	0,5	2,5	-	62,20 €
CF5UUR/SS	5	13	9	M5 x 0,8	7,5	10,0	23,0	13,0	-	0,5	3	✔	58,25 €
CF6UUR/SS	6	16	11	M6 x 1	8,0	12,2	28,2	16,0	-	0,6	3	✔	54,50 €
CF8UUR/SS	8	19	11	M8 x 1,25	10,0	12,2	32,2	20,0	-	0,6	4	✔	56,00 €
CF10UUR/SS	10	22	12	M10 x 1,25	12,0	13,2	36,2	23,0	-	0,6	4	✔	56,00 €
CF12UUR/SS	12	30	14	M12 x 1,5	13,0	15,2	40,2	25,0	6	0,6	6	✔	70,15 €
CF16UUR/SS	16	35	18	M16 x 1,5	17,0	19,6	52,1	32,5	8	0,8	6	✔	83,55 €
CF18UUR/SS	18	40	20	M18 x 1,5	19,0	21,6	58,1	36,5	8	0,8	8	✔	102,05 €
CF20UUR/SS	20	52	24	M20 x 1,5	21,0	25,6	66,1	40,5	9	0,8	8	✔	137,96 €

**Depending on avaibility - Dimensions in mm*