

Module 0,5

Laiton CuZn39Pb3

NOUVEAU !


- Engrenage droit denture JIS
grade 8 (JISB1702-1:1998)



- Angle de pression 20°

- Matière :

Laiton CuZn39Pb3 (C6304)

Info

- *Couple (bending strength)


REMISES

Qté	1+	6+	10+
Rem.	Prix	-12%	Sur demande

Références	Z	ØP	ØD	ØM	ØA alésage		E	F	G	ØT	J	Couple* (Nm)	Masse (kg)	Prix Uni. 1 à 5
GB0,5-15-RA03T	15	7,5	8,5	8,5	3	3	11	14	M3	2,5	0,058	0,005		
GB0,5-16-RA03T	16	8,0	9,0	9,0	3	3	11	14	M3	2,5	0,065	0,006		
GB0,5-18-RA03T	18	9,0	10,0	10,0	3	3	11	14	M3	2,5	0,078	0,008		
GB0,5-20-RA04	20	10,0	11,0	8,5	4	3	7	10	-	-	0,091	0,004		
GB0,5-20-RA03T	20	10,0	11,0	11,0	3	3	11	14	M3	2,5	0,091	0,010		
GB0,5-20-RA04T	20	10,0	11,0	11,0	4	3	11	14	M3	2,5	0,091	0,009		
GB0,5-22-RA03T	22	11,0	12,0	9,0	3	3	7	10	M3	3,5	0,10	0,005		
GB0,5-24-RA04T	24	12,0	13,0	10,0	4	3	7	10	M3	3,5	0,12	0,006		
GB0,5-25-RA04	25	12,5	13,5	11,0	4	3	7	10	-	-	0,12	0,008		
GB0,5-26-RA03T	26	13,0	14,0	10,0	3	3	7	10	M3	3,5	0,13	0,007		
GB0,5-27-RA03T	27	13,5	14,5	10,0	3	3	7	10	M3	3,5	0,14	0,008		
GB0,5-28-RA03T	28	14,0	15,0	12,0	3	3	7	10	M3	3,5	0,15	0,010		
GB0,5-30-RA04	30	15,0	16,0	13,0	4	3	7	10	-	-	0,16	0,011		
GB0,5-30-RA03T	30	15,0	16,0	12,0	3	3	7	10	M3	3,5	0,16	0,010		
GB0,5-30-RA04T	30	15,0	16,0	12,0	4	3	7	10	M3	3,5	0,16	0,010		
GB0,5-30-RA05T	30	15,0	16,0	12,0	5	3	7	10	M4	3,5	0,16	0,009		
GB0,5-38-RA04T	38	19,0	20,0	16,0	4	3	7	10	M3	3,5	0,22	0,018		
GB0,5-40-RA04	40	20,0	21,0	17,0	4	3	7	10	-	-	0,23	0,020		
GB0,5-40-RA05T	40	20,0	21,0	18,0	5	3	7	10	M4	3,5	0,23	0,021		
GB0,5-50-RA04T	50	25,0	26,0	22,0	4	3	7	10	M3	3,5	0,31	0,033		
GB0,5-50-RA05T	50	25,0	26,0	22,0	5	3	7	10	M4	3,5	0,31	0,032		
GB0,5-60-RA05T	60	30,0	31,0	28,0	5	3	7	10	M4	3,5	0,38	0,052		
GB0,5-60-RA06T	60	30,0	31,0	28,0	6	3	7	10	M4	3,5	0,38	0,051		
GB0,5-70-RA05T	70	35,0	36,0	28,0	5	3	7	10	M4	3,5	0,46	0,058		
GB0,5-80-RA05T	80	40,0	41,0	28,0	5	3	7	10	M4	3,5	0,54	0,065		
GB0,5-80-RA06T	80	40,0	41,0	28,0	6	3	7	10	M4	3,5	0,54	0,065		

Dimensions en mm