


- **Axle mounted eccentric cam follower**
- Synthetic rubber joints fitted to external ring
- Assemble using a screwdriver
- Diameter of housing 6 to 18mm, tolerance H7
- Material: carbon steel

Info.

- All the followers come with grease nipples: at the end of the axle on the roller side, on the threaded side, and on the cylindrical section,
(Except for cam < 10 mm with only one hole on the roller side).



Adjustable backlash



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Part number	Min. flange Ø f (mm)	Torque (Nm)	C (N) Basic static load C (N)	Max. admissible load (N)	Max. speed (l) (rpm)	Øg1 (mm)	g2 (mm)	r mini. (mm)	Eccen- tricity ε (mm)
CFES6UUR	11	12,7	3660	3650	1980	-	-	0,3	0,25
CFES8UUR	13	6,5	4250	4740	4670	-	-	0,3	0,25
CFES10UUR	16	13,8	5430	6890	6890	-	-	0,3	0,30
CFES10-1UUR	16	13,8	5430	6890	6890	-	-	0,3	0,30
CFES12UUR	21	21,9	7910	9790	9790	4	3	0,6	0,40
CFES12-1UUR	21	21,9	7910	9790	9790	4	3	0,6	0,40
CFES16UUR	26	58,5	12000	18300	18300	4	3	0,6	0,50
CFES18UU	29	86,2	14800	25200	25200	6	3	1,0	0,60

Part number	d1 (h7)	D (h5)	C ^{+0.12} -0.12	G	G1	B	B1	B2	B3	C1	Stock*	Price each 1 to 5
CFES6UUR	6	16	11	M6 x 1,00	8	12,2	28,2	16,0	-	0,6	✓	36,38 €
CFES8UUR	8	19	11	M8 x 1,25	10	12,2	32,2	20,0	-	0,6	✓	37,82 €
CFES10UUR	10	22	12	M10 x 1,25	12	13,2	36,2	23,0	-	0,6	✓	41,76 €
CFES10-1UUR	10	26	12	M10 x 1,25	12	13,2	36,2	23,0	-	0,6	✓	44,12 €
CFES12UUR	12	30	14	M12 x 1,50	13	15,2	40,2	25,0	6	0,6	-	47,12 €
CFES12-1UUR	12	32	14	M12 x 1,50	13	15,2	40,2	25,0	6	0,6	-	41,70 €
CFES16UUR	16	35	18	M16 x 1,50	17	19,6	52,1	32,5	8	0,8	-	56,70 €
CFES18UU	18	40	20	M18 x 1,50	19	21,6	58,1	36,5	8	0,8	✓	67,32 €

*Depending on availability - Dimensions in mm