

- **Stainless steel range**
- **Plain pins and bushes**
- Suitable for speeds up to 800 rpm
- Max. angle of misalignment 90°
- Material:
Stainless steel X5CrNi1810

Uses


- Food and pharmaceutical industries

Accessories

- Optional rubber cover



modifiable bore-size



Angle	Factor
5°	1,25
10°	1,00
20°	0,75
30°	0,45
40°	0,30

Effect of operating angle

The torques below are given for a 10° angle. For other angles, the appropriate factor from this table should be applied.
E.g. For 10Nm to be transmitted at 20°, the corrected value of torque becomes $10/0.75 = 13.3$ Nm and a joint should be chosen that can transmit 13.3Nm at the required speed.

DISCOUNTS

Qty.	1+	5+	10+	25+	50+
Disc.	List	-6%	-12%	-18%	On request

Part number	ØD	ØA	C	M	L	Torque (Nm)								Price each 1 to 4
						at 100 rpm	at 200 rpm	at 300 rpm	at 400 rpm	at 500 rpm	at 700 rpm	at 800 rpm	Stock*	
JCD04/SS	22	12	25	29	105	18,9	11,34	9,00	7,20	6,57	5,67	5,22	✓	88,68 €
JCD05/SS	25	14	29	33	119	29,7	19,17	17,37	15,84	14,67	11,97	11,34	-	92,25 €
JCD06/SS	29	16	30	35	125	40,5	37,80	31,77	25,20	22,77	18,00	15,57	✓	95,76 €
JCD07/SS	32	18	30	39	134	68,4	54,00	41,94	31,77	26,37	20,97	-	-	113,51 €
JCD08/SS	40	20	32	46	154	105,3	75,60	52,74	41,94	37,17	26,37	-	✓	124,15 €
JCD09/SS	40	22	38	46	173	131,4	86,40	63,00	52,74	41,94	31,77	-	-	156,11 €
JCD10/SS	50	25	44	59	199	172,8	108,00	75,60	64,80	54,00	43,20	-	-	184,53 €
JCD11/SS	58	30	58	66	244	194,4	118,80	86,40	70,20	59,40	-	-	-	241,30 €

*Depending on availability - Dimensions in mm