

Hub clamp

MDS

Shaft positioning

- For positioning or holding a shaft

- Material :




Blackened steel 1.1206

Application

Hub clamp can be quickly and easily attached to shafts, adjusted to the proper operating position and then locked.

Assembly

For proper torque transfer, an h11 shaft tolerance is recommended



DISCOUNTS

Qty	1+	5+	10+	25+	50+
Disc.	List	-6%	-12%	-18%	On request

Part number	ØD	ØD1	M	ØD3	B	B1	L	T	Approx weight	Price each 1 to 4
MDS10-36	10	24	M8	10	15,5	13	36	11	0,078	20,45 €
MDS12-36	12	24	M8	10	15,5	13	36	11	0,074	20,45 €
MDS12-41	12	28	M10	12	17,5	15	41	14	0,118	23,16 €
MDS14-41	14	28	M10	12	17,5	15	41	14	0,113	23,16 €
MDS14-45	14	32	M12	14	19,5	17	45	16	0,169	28,62 €
MDS16-45	16	32	M12	14	19,5	17	45	16	0,162	28,62 €

Dimensions in mm