

Applications

- Motor driven pumps or compressors
- Electrical generators, textile machines
- Iron and steel plants, cement factories.

Determining torque

$$T_{MN} = \frac{N_{kW} \times 9550}{n_{rpm}} = (Nm)$$

Service factor K :

Service	Electric motor steam turbine	Combustion engine hydraulic turbine
Uniform S1	1,0	1,5
Light S2	1,5	2,0
medium S3	2,0	2,5
Heavy S4	2,5	3,0
Very heavy S5	3,0	3,2

Temperature factor St:

St	-20°C	0°C	+20°C	+40°C	+60°C	+70°C	+80°C
	1,0	1,0	1,0	1,0	1,2	1,4	1,6

$$T_{MN} \times K \times St \leq T_{CN} \text{ coupling}$$

$$n_{inst.} \leq n_{MAX} \text{ coupling}$$

$$\text{shaft diameter} \leq d_{MAX} \text{ coupling}$$

Safety precautions

The tyre is cut radially to allow mounting/dismounting. Depending on the speed and torque transmitted, an axial force will be generated which must be absorbed by the bearings in the coupled machines. The tyre may expand by up to 5% during use which must be taken into account when choosing a protective housing.



Part number	Nominal torque TCN (Nm)	Max. torque TCmaxi. (Nm)	Max. speed (rpm)	Moment of inertia (kgm²)	Axial (Nm)	Misalignment Radial (Nm)	Angular
PNA2-203R	50	150	5 000	0,001	1,0	0,75	2°
PNA6-206R	100	300	5 000	0,003	1,5	1,00	2°
PNA16-210R	200	600	4 000	0,013	2,0	1,30	2°
PNA40-214R	400	1 200	4 000	0,035	2,5	1,60	2°
PNA63-218R	800	2 400	3 000	0,105	3,0	2,10	2°

Dimensions in mm

PERIFLEX® elastic coupling

Torque: 50 to 2400Nm

PNA


- Easy installation, machines to be coupled will not require to be moved
- Backlash free
- Can transmit shocks up to 3 times the value of nominal torque
- Quickly damps vibrations
- Maintenance free

Characteristics

- Large axial misalignment up to 6mm
radial up to 5mm
angular up to 2°
- Keyway in accordance with
NF E22-175/P9 (JS9)
- Working temp.: -20°C to +80°C
- Materials:
Hub: Steel
Locking assembly: Steel
Tyre R: Natural rubber (NR) with
fabric reinforcements

Options

- Alternative tyre materials (inserts
mounted in X pattern)



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number solid coupling	ØA	ØB	ØC	L	M	Ød max.	Ød pre-bore	Ød Standard bores (H7)
PNA2-203R	104	54	40	70	30	28	plein	10, 15, 19, 20, 25, 28
PNA6-206R	136	68	55	110	45	38	plein	10, 15, 20, 25, 30, 35, 38
PNA16-210R	178	88	70	130	50	48	15	20, 25, 30, 35, 38, 48
PNA40-214R ⁽¹⁾	210	116	92	160	65	65	15	20, 25, 30, 35, 40, 45, 50, 55, 60, 65
PNA63-218R ⁽¹⁾	263	140	107	190	75	75	25	30, 35, 40, 45, 50, 55, 60, 65, 70, 75

Part number solid coupling	N	O	P	Number of screws	Screw	Locking torque (Nm)	Weight (kg)	Stock* prebored	Price each full or bored	Price each keyway
PNA2-203R	8	16	66	12	M6	4 ⁽²⁾	1,15	✓	335,76 €	568,57 €
PNA6-206R	8	18	74	16	M6	6 ⁽²⁾	2,50	✓	445,46 €	702,92 €
PNA16-210R	19	35	100	16	M8	15 ⁽²⁾	5,40	✓	564,12 €	823,79 €
PNA40-214R ⁽¹⁾	20	38	99	24	M8	20	9,50	-	821,56 €	1 096,93 €
PNA63-218R ⁽¹⁾	24	44	121	16	M12	25	17,50	-	1 121,57 €	1 464,09 €

*Depending on availability - Dimensions in mm

Fax: 0 825 88 6000 > Service 0,15 €/min + prix appel

cial2@hpceurope.com

WEB
04/2020

HPC