Alu Size XS 1 2 3 Stock


T-type timing pulley

Aluminium

Pitch T2.5

Belt width 6mm

- **Pitch 2.5mm**
- Matierials:
  Pulley: Aluminium 6082
  Flanges: Aluminum for pulleys with up to 84 teeth, steel for 85 teeth or more
- All pulleys have flanges



Options

- **Choose from 10 to 230 teeth**

bore-size, keyway
MODIFY IT!
tapped hole, pin, etc...

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	Ø PCD	ØD	ØM	ØA	Flange ref.	ØE	Stock*	Price each 1 to 5 T	Price each 1 to 5 PT
10T2.5-10	10	7,96	7,40	13	3	10 X,Y	13,00	✔	On request	On request
12T2.5-10	12	9,55	9,00	13	3	10 X,Y	13,00	✔		
14T2.5-10	14	11,14	10,60	18	3	16 X,Y	18,00	✔		
15T2.5-10	15	11,94	11,40	18	3	16 X,Y	18,00	✔		
16T2.5-10	16	12,73	12,20	18	4	16 X,Y	18,00	✔		
18T2.5-10	18	14,32	13,80	18	4	31 X,Y	18,00	✔		
19T2.5-10	19	15,12	14,60	20	4	32 X,Y	20,00	-		
20T2.5-10	20	15,92	15,40	20	4	32 X,Y	20,00	-		
21T2.5-10	21	16,71	16,20	20	4	32 X,Y	20,00	-		
22T2.5-10	22	17,51	17,00	20	4	32 X,Y	20,00	✔		
24T2.5-10	24	19,10	18,55	13	4	12 XL	25,15	✔		
25T2.5-10	25	19,89	19,35	13	4	12 XL	25,15	-		
26T2.5-10	26	20,69	20,15	13	5	12 XL	25,15	✔		
30T2.5-10	30	23,87	23,35	20	5	16 XL	31,74	-		
31T2.5-10	31	24,67	24,15	20	5	18 XL	34,80	-		
32T2.5-10	32	25,46	24,95	20	5	18 XL	34,80	✔		
40T2.5-10	40	31,83	31,30	24	6	21XL	39,68	✔		
44T2.5-10	44	35,01	34,50	24	6	21XL	39,68	-		
48T2.5-10	48	38,20	37,70	24	6	24XL	44,70	-		
52T2.5-10	52	41,38	40,85	24	6	24XL	44,70	-		
57T2.5-10	57	45,36	44,85	24	6	28XL	51,05	-		
60T2.5-10	60	47,75	47,25	24	6	30XL	54,36	-		
80T2.5-10	80	63,66	63,16	24	6	17H	74,61	✔		
84T2.5-10	84	66,85	66,35	24	6	18H	79,38	-		
↓	Pulleys available up to this size								↓	
230T2,5-10	230	Dimensions : contact us								

*Depending on availabiliity - Dimensions in mm