

Manual lifting tables







TBV1 For vertical strokes - Ø 12 mm column

Manually operated leadscrew table

- Right handed leadscrew TR10x2
- 12 mm diameter guide rods
- Fixed by the extremities for vertical or off-centred applications
- Guided by 2 steel rods on 4 brass bearings (no wiper joints)
- With position indicator and button
- Axial precision <0.15 mm
- Material:
Aluminium, steel
- Working temperature range:
+5° to +80 °C

Accurate to 0.1 mm



DISCOUNTS

Qty	1+	2+	3+
Disc.	List -10%	On request	

Part number	Stroke	Guide rod	Max supported load (kg)	Moving torque on hand wheel (Nm)	Indication for 1 rev	Weight* (kg)	Price each
TBV1-50-CV	50	TR10x2	3	0,30	002,0	1,20	498,42 €
TBV1-100-CV	100	TR10x2	3	0,30	002,0	1,31	498,42 €
TBV1-150-CV	150	TR10x2	3	0,30	002,0	1,42	502,03 €
TBV1-200-CV	200	TR10x2	3	0,30	002,0	1,53	502,03 €
TBV1-300-CV	300	TR10x2	3	0,30	002,0	1,75	505,67 €

*Weight without hand wheel or indicator - Dimensions in mm





Manual lifting tables



TBV2 For vertical strokes – Ø16 mm column

- **Manually operated leadscrew table**
- Right handed leadscrew TR12x3
- 16mm diameter guide rods
- Fixed by the extremities for vertical or off-centred applications
- Guided by 2 steel rods on 4 brass bearings (no wiper joints)
- With position indicator and hand wheel
- Axial precision <0.15 mm
- Material:
Aluminium, steel
- Working temperature range:
+5° to +80°C

Accurate to 0.1mm



DISCOUNTS

Qty	1+	2+	3+
Disc.	List -10%	On request	

Part number	Stroke	Guide rod	Max supported load (kg)	Moving torque on hand wheel(Nm)	Indication for 1 rev	Weight* (kg)	Price each
TBV2-50-CV	50	TR12x3	7	0,45	003,0	2,11	544,49 €
TBV2-100-CV	100	TR12x3	7	0,45	003,0	2,29	544,49 €
TBV2-150-CV	150	TR12x3	7	0,45	003,0	2,47	550,40 €
TBV2-200-CV	200	TR12x3	7	0,45	003,0	2,65	550,40 €
TBV2-300-CV	300	TR12x3	7	0,45	003,0	3,01	556,31 €

*Weight without hand wheel or indicator - Dimensions in mm







Manual lifting tables



TBV4 For vertical strokes - Ø25 mm column

- **Manually operated leadscrew table**
- Right handed leadscrew TR16x4
- 25 mm diameter guide rods
- Fixed by the extremities for vertical or off-centred applications
- Guided by 2 steel rods on 4 brass bearings (no wiper joints)
- Axial precision (in locked position) <0.05 mm
- With position indicator and hand wheel
- Axial precision <0.15 mm
- Material:
Aluminium, steel
- Working temperature range:
+5 to + 80°C

Accurate to 0.1 mm



DISCOUNTS

Qty	1+	2+	3+
Disc.	List -10%	On request	

Part number	Stroke	Guide rod	Max supported load (kg)	Moving torque on hand wheel (Nm)	Indication for 1 rev	Weight* (kg)	Price each
TBV4-50-CV	50	TR16x4	20	1,25	004,0	7,28	821,26 €
TBV4-100-CV	100	TR16x4	20	1,25	004,0	7,73	821,26 €
TBV4-150-CV	150	TR16x4	20	1,25	004,0	8,18	831,48 €
TBV4-200-CV	200	TR16x4	20	1,25	004,0	8,63	831,48 €
TBV4-300-CV	300	TR16x4	20	1,25	004,0	9,53	841,69 €

*Weight without hand wheel or indicator - Dimensions in mm