



Plastic bevel gear

Moulded nylon PA6

Ratio
1:1


- **Module 1 to 3.5**
- Moulded parts
- Material: Nylon 6 reinforced with 30% glass fibre
- Rough pilot bore after moulding

Options


- We are unable to modify these parts

Info.

- The 2 bevels should form a matching pair
- Moulded pre-bore must be machined to suit the application
- *Pilot bore dimension given as a guide only



ϕA :
pilot bore
requires
finishing



Economy range

DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Teeth		Pilot bore no guaranteed							L	Lm	Stock*	Price each 1 to 9
	Z	Module	ØDe	ØDp	B	F	ØDn	dm	ØA*				
MEB1-16	16	1,0	17,8	16,0	14,0	4	13	18,59	5	14,0	9,0	✓	4,39 €
MEB1.5-16	16	1,5	25,0	24,0	18,0	6	20	25,10	8	17,0	8,9	✓	5,32 €
MEB1.5-20	20	1,5	32,1	30,0	20,0	8	22	28,70	6	18,0	9,0	✓	6,25 €
MEB1.5-30	30	1,5	47,1	45,0	25,0	10	35	39,70	12	22,5	12,0	✓	9,21 €
MEB2-16	16	2,0	34,8	32,0	20,0	9	25	28,80	10	17,0	9,3	✓	7,54 €
MEB2-20	20	2,0	42,8	40,0	27,0	12	32	35,70	8	22,0	12,0	✓	10,68 €
MEB2-30	30	2,0	62,8	60,0	30,0	16	50	47,80	12	27,0	12,8	✓	12,20 €
MEB2.5-16	16	2,5	43,5	40,0	27,0	10	30	37,30	12	22,0	13,3	✓	9,59 €
MEB2.5-20	20	2,5	53,5	50,0	30,0	12	38	45,90	12	27,0	16,0	✓	11,42 €
MEB2.5-30	30	2,5	78,5	75,0	35,0	18	50	59,10	14	32,0	16,0	-	16,08 €
MEB3-16	16	3,0	52,2	48,0	30,0	12	38	44,20	11	26,0	16,2	-	14,03 €
MEB3-20	20	3,0	64,2	60,0	35,0	18	44	51,10	14	31,0	13,6	✓	15,15 €
MEB3-30	30	3,0	94,2	90,0	40,0	22	60	68,10	20	36,0	19,0	✓	19,79 €
MEB3.5-20	20	3,5	74,9	70,0	40,5	22	56	58,60	58,60	36,0	19,0	-	17,57 €

*Depending on availability - Dimensions in mm