

H Type guide unit







UGH16 For $\text{Ø}12 + \text{Ø}16$ actuators (ISO 6432)

- Guide system for actuator
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling available on front face
- Supplied with fixing screw for actuator
- Maintenance free
- Working temperature: +5 to +80 °C
- Maximum speed: 1 m/s
- Maximum loads: See end of section
- Material:

Body + face plate:
anodised aluminium
Couplings + screws:
Zinc plated steel
Guide shafts:
Chromed steel

Excellent price/
Quality ratio

Accurate even over
long strokes



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke	Ø Actuator	Ø Guide rod	Weight (kg)	Price each
UGH16-25	25	12 et 16	10	0,43	183,01 €
UGH16-50	50	12 et 16	10	0,46	183,97 €
UGH16-100	100	12 et 16	10	0,52	185,88 €
UGH16-160	160	12 et 16	10	0,59	188,15 €
UGH16-200	200	12 et 16	10	0,64	189,67 €
UGH16-250	250	12 et 16	10	0,70	191,63 €

Dimensions in mm