

H Type guide unit



UGH20





For **Ø20** actuators (ISO 6432)

- Guide system for actuator
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling available on front face
- Supplied with fixing screw for actuator
- Maintenance free
- Working temperature: +5 to +80 °C
- Maximum speed: 1 m/s
- Maximum loads: See end of section
- Material:

Body + face plate:
anodised aluminium
Couplings + screws:
Zinc plated steel
Guide shafts:
Chromed steel

**Excellent price/
Quality ratio**

**Accurate even over
long strokes**



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke	Ø Actuator	Ø Guide rod	Weight (kg)	Price each
UGH20-25	25	20	10	0,93	201,98 €
UGH20-50	50	20	10	0,96	202,91 €
UGH20-100	100	20	10	1,02	204,78 €
UGH20-160	160	20	10	1,09	207,07 €
UGH20-200	200	20	10	1,14	208,66 €
UGH20-250	250	20	10	1,20	210,54 €

Dimensions in mm