

Panel mounting block for aluminium structures

ACL_{FPA} Angular joint and mounting block

- Support for glazed panel, multiple blocks can be used to create angled joints

- Materials:

- Injection moulded zinc, aluminium sprayed coating
- Block supplied with 5 rubber pads for panel thicknesses from 2 to 5 mm

Assembly

- Insert the PRF-ECL-M5 nut (supplied separately) into the slot of the aluminium profile.
- Attach the first side of the block using the M5 screw supplied.
- Attach the rubber mounting pads
- Tighten the second side of the mounting block
- When creating an angled joint, attach the first sides of each block, then attach the rubber mounting pads and then fix the second sides.




ACL-FPA-BM




ACL-FPA-RA



Typical application
ACL-FPA-BM



ACL-FPA-BM



ACL-FPA-RA



ACL-FPA-BM + ACL-FPA-RA

DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Type	Weight (g)	Price each 1 to 49
ACL-FPA-BM	Support bloc	74	9,88 €
ACL-FPA-RA	Angular joint	37	6,10 €

Dimensions in mm

Our other products



F7-P-AM
Multifunction display,
Magnetic band



SUA4_L
Chain link, Steel



BPH
Ball transfer unit plain
fit, High



BABreglable
Adjustable ball pin
hardened stainless
steel, adjustable



PR125rehausse
Extension for
articulated foot Ø123,
articulated foot PR125



GCL
Linear ball slide Eco
Range, economy
range




MDB_MTB
Moulded plastic bevel
gear (nylon), 2:1



H3
Crossed helical gear
crossed axis at 90°,
Machined plastic
(delrin)



PTAF100-PAMF100
Articulated fixable
foot with pressed



PF45
Worm and wheel gear
reducer, up to 40 Nm



CHA225
Screwed hinge with
threaded insert, 225



UGH20
H Type Guide units,
For Ø20 actuators

Complementary products



PRF_ECL
Nut for aluminium
profile, Steel square
nut with tab



ACL-FPA
Panel mounting block
for aluminium
structures, Angular
connector