


- **Plastic construction**
- Light weight
- Low cost version
- Corrosion resistant
- Available in 2 sizes
- Supplied without handle




Part number	Max stroke [mm]	Aluminium profile Weight [kg]	Add weight (/0.1m stroke)	Notes
SHTP-01-06	300	0,11	0,06	Square carriage with 4 symmetrical mounting holes
SHTP-01-12	750	0,35	0,11	Smooth guides and nuts in iglidur®J
SHTP-02-12	750	0,35	0,11	-

Part number	A	Al	H	E1	E2	L	R	f	lt	tk	ts
SHTP-01-06	45	45	19	38	36,5	67	25	1	11	8	4,2
SHTP-01-12	85	30	36	70	73,0	90	42	2	30	10	6,6
SHTP-02-12	85	30	36	70	73,0	90	42	2	30	10	6,6

Part number	s	sg	d	T	I2	d2* standard	ha	H1
SHTP-01-06	5,0	-	6	M8	15	M8	9	18
SHTP-01-12	6,3	M6	12	TR10x2	17	TR10x2	16	32
SHTP-02-12	6,3	M6	12	TR10x2	17	TR10x2	16	32

Dimensions in mm

Economical



DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-10%	On request

Part number	Stroke (mm)	Stock*	Price each
SHTP-01-06-100	100	✓	105,45 €
SHTP-01-06-250	250	✓	132,76 €
SHTP-01-12-100	100	✓	146,51 €
SHTP-01-12-250	250	✓	183,14 €
SHTP-01-12-500	500	-	219,30 €
SHTP-02-12-100	100	✓	111,31 €
SHTP-02-12-250	250	✓	138,62 €
SHTP-02-12-500	500	-	184,11 €

Dimensions in mm