Horizontal toggle clamp

With locking mechanism — SLHV LOK

High quality swivel bush with horizontal foot and adjustable spindle

Constant level of force during both opening and closing

Increased stability thanks to U-shaped clamping arm


Fitted with automatic locking mechanism

-Material :


Nitro carburised steel with blackened finish

Polyamide handle


Locking mechanism TPE



Vertical base







Hole positions

DISCOUNTS

Qty	1+	6+	15+	20+
Disc.	List	-5%	-10%	On request

Part number	Opening angle Holding arm	Handle	Manual force N	Holding force F1 (N)	Holding force F2 (N)	Clamping force F3 (N)	Clamping force F4 (N)	H	H1	L	L1
SLHV-6/LOK	87°	68°	160	1350	1900	720	1200	74,3	71	193,7	60,5
SLHV-8/LOK	86°	66°	200	2000	2800	830	1400	88,3	84,4	230,3	74,9
SLHV-10/LOK	90°	71°	250	2200	4500	1200	2800	114,4	107,5	286,4	103,9
SLHV-12/LOK	88°	68°	280	2400	5500	1000	2800	128,5	125,2	321,3	122

Part number	M	A	A1	A2	A3	A4	B	B1	B2	B3	B6	C	C2	ØD	Price each 1 to 5
SLHV-6/LOK	M6x35	26	39	6,5	-	2,5	14,1	9,1	17,5	12,4	53,4	37	5,5	5,5	51,38 €
SLHV-8/LOK	M8x45	26	44	9	-	3,5	14,1	9,1	21	15,7	51,1	46,5	7	6,2	52,31 €
SLHV-10/LOK	M10x55	41,5	59	9	-	2	16,2	9,2	26	18,7	56,5	59,6	8	8,8	70,14 €
SLHV-12/LOK	M12x70	44	65	10	40	1	16,2	9,2	28	20,9	56,5	75,9	13,5	8,5	73,16 €

Dimensions in mm