
Screwjack with translating screw ★★★

SVT30 — Nominal load 30,000N

- ***Standard stroke length: 100mm***
- *Material:*
  Body: Iron GGG50
- *Weight (without screw): 8.2 kg*
- *Weight of screw: 0.43 kg /100mm*
- *Lubrication: Grease (200g required)*


Accessories

- *Plate* **SVT30-PLATEAU**
- *Clevis* **SVT30-CHAPE**




SVT30-H





SVT30-B



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Reduction ratio	Torque at nominal force (Nm)	Efficiency	rpm max.	Max. speed (m/min)	Max. power (kW) at 20% DC	Max. power (kW) at 10% DC
SVT30-6	6:1	16,5	29%	2800	2,8	0,6	0,8
SVT30-24	24:1	7,0	17%	2800	0,7	0,6	0,8

Part number	Reduction ratio	Stroke (H)	Screw Ø	Stroke per rev (mm)	Nominal force (N)	Price each
Upwards direction						
SVT30-6-100H	6:1	100	TR30 x 6	1,00	30000	1 125,24 €
SVT30-24-100H	24:1	100	TR30 x 6	0,25	30000	1 125,24 €
SVT30-COURSE	per additional 100mm of stroke length					21,86 €
Downwards direction						
SVT30-6-100B	6:1	100	TR30 x 6	1,00	30000	1 125,24 €
SVT30-24-100B	24:1	100	TR30 x 6	0,25	30000	1 125,24 €
SVT30-COURSE	per additional 100mm of stroke length					21,86 €

Dimensions in mm