


H Type guide unit



UGH25

For **Ø25** actuators ISO 6432




- Guide system for standard pneumatic actuators
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper seals
- Actuator coupling supplied
- Maintenance free
- Working temperature: +5°C to +80°C
- Maximum speed: 1 m/s
- Maximum loads : See end of section



Material

- Body + face plate: anodised aluminium
- Couplings + screws: Zinc plated steel
- Shafts: Chromed steel

Accurate even for long strokes



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke (mm)	Actuator Ø (mm)	Guide rod Ø (mm)	Weight (kg)	Price each
UGH25-25	25	25	10	0,93	201,98 €
UGH25-50	50	25	10	0,96	202,89 €
UGH25-100	100	25	10	1,02	204,78 €
UGH25-160	160	25	10	1,09	207,07 €
UGH25-200	200	25	10	1,14	208,64 €
UGH25-250	250	25	10	1,20	210,52 €

Dimensions in mm