



Bellow coupling


Couplings for servo-motors

GERWAH AK

Torque: **36 to 800Nm**

- Backlash and maintenance free
- High torsional stiffness
- Low moment of inertia
- Shaft/bore link without backlash
- Recommended assembly tolerances H7/g6
- Working temperature -30°C to +100°C
- Materials:
 - Hub: steel
 - Bellows: stainless steel
- Please specify bore size on order (between min and max Ø)

clamp fixing



Torque calculation

- Use the formula

$$T_{KN} > K \times T_{AS} \times J_{mach} / (J_{mot} + J_{mach}) \text{ in Nm}$$

With following safety coefficient:


K = 1.5 for regular motion

K = 2 for irregular motion

K = 2.5 - 4 for jerky motion

Jx = moment of inertia (machine + motor)

T_{AS} Required torque



High Precision

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-6%	On request

Part number	Nominal torque (Nm)	Stiffness			Moment of inertia (10 ⁻³ kgm ²)	Tightening torque (Nm)	Weight (kg)	Misalignment			Max. speed (rpm)
		torsional (10 ³ Nm/Rad)	radial (N/mm)	axial (N/mm)				radial (mm)	axial (mm)	angular (°)	
AK30-60	36	25	220	30	0,15	3,0	0,28	0,2	0,5	1,5	11 000
AK60-73	72	50	330	55	0,24	8,5	0,48	0,2	0,5	1,5	9 100
AK80-91	96	75	400	55	0,65	10,0	0,85	0,2	0,5	1,5	7 000
AK150-92	180	100	600	85	0,65	14,0	0,85	0,2	0,5	1,5	7 000
AK200-93	240	120	450	85	0,87	14,0	1,00	0,2	0,5	1,5	6 700
AK300-104	360	280	1500	150	2,33	18,0	1,92	0,2	0,5	1,5	5 200
AK500-113	800	310	1000	85	5,73	26,0	2,45	0,2	1,0	1,5	4 600

Part number	ØA (mm)	ØB (mm)	L	D ^{H7} /D ^{h7}		E	J	ØT	G	Price each
				min.	max.					
AK30-60	56	55	60	9	20	53	38	31	6 x M4	263,16 €
AK60-73	66	64	73	12	25	65	46	37	6 x M6	285,51 €
AK80-91	82	80	91	15	35	83	61	51	6 x M6	313,72 €
AK150-92	82	80	91	15	35	84	61	51	6 x M6	366,36 €
AK200-93	90	90	93	15	42	85	63	56	6 x M6	428,96 €
AK300-104	110	110	104	15	50	93	67	75	6 x M8	495,88 €
AK500-113	122	119	113	24	55	105	72	80	6 x M8	645,52 €

Dimensions in mm

Our other products



PRF4545_P

Stripp Aluminium profile with extendable slot, 45 x 45 mm



SLV

Vertical toggle clamp, Vertical Lever Clamp - steel




VPPTss

Stainless steel handwheel with handle, Stainless steel 304



CHAsb89

Hinge without pin, Plastic hinge



G1

Steel spur gear, Steel 20NCD2



RJUM05

Drylin R® linear bearing housing, Closed - Slim



SER

Magnetic doorstop for aluminium profile, Magnetic doorstop



PSG25S

Spur gear - precision range, Stainless steel 303



HLUT

Spoked handwheel with handle, Aluminium




PSG25

Spur gear - precision range, Pre-hardened Steel 35NCD6



GGB

Female wing knob, With blind thread



RDERS5

Stainless steel manual rigging screw, Stainless steel - manual

Complementary products