




H Type guide unit

For $\varnothing 32$ actuators
ISO (VDMA 24562)


UGH32

- Guide system for standard pneumatic actuators
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling supplied
- Fixing holes conform to CNOMO standards
- Supplied with 4 fixing screws for actuator
- Maintenance free
- Working temperature: +5°C to +80°C
- Maximum speed: 1 m/s
- Maximum loads : See end of section




Material

- Body + face plate: anodised aluminium
- Couplings + screws: Zinc plated steel $\varnothing 12$
- Guide shafts: Chromed steel



Accurate even for long strokes



Attach cylinder using 4 off M6 screws on $\varnothing 32.5$

DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke (mm)	Actuator \varnothing (mm)	Guide rod \varnothing (mm)	Weight (kg)	Price each
UGH32-25	25	32	12	1,34	204,11 €
UGH32-50	50	32	12	1,38	205,16 €
UGH32-100	100	32	12	1,47	207,20 €
UGH32-160	160	32	12	1,57	209,70 €
UGH32-200	200	32	12	1,64	211,35 €
UGH32-250	250	32	12	1,72	213,37 €
UGH32-320	320	32	12	1,84	216,29 €
UGH32-400	400	32	12	1,98	219,61 €
UGH32-500	500	32	12	2,15	223,74 €
UGH32-600	600	32	12	2,32	227,84 €

Dimensions in mm