

Advantages

- Universal Mains supply.
PF>0.98@115Vac, PF>0.95@230Vac
- Protected against short circuits, overloads and over-voltage
- Switching frequency : 100KHZ
- UL508 listed
- Din rail mounting, DINTS35/7.5 or 15.
- LED supply indication
- Air-cooled
- 100% Burn-in

Characteristics

- Output voltage can be varied from 24 to 48V DC
- Max ripple on output +/- 1%

Protections

- Max overload on output limited to 105 to 150%
- Output is short circuit protected
- Max overvoltage on output 30 to 36 V DC

Environment


- EMC: Conforms to EN55022 class B, EN61000-3-2,3, EN61000-6-2, EN61000-4-2,3,4,5,6,8,11, ENV50204, EN61204-3
- Personnel safety: Conforms to UL508, UL60950-1, TUV60950-1
- Max working temperature -10° to +50°C @100% load, +70°C @60% load (natural convection)

Connection

- Supply: 3 screw clamp terminals DIN
- Output: 4 screw clamp terminals DIN

Dimensions/Material

- Enclosure: painted plastic
- Dimensions 125.5 x 125.2 x 100 (L x W x H)



DISCOUNTS

Qty	1+	6+	10+
Disc. List	-7%	On request	

Part number	Supply voltage (V AC)	Output voltage (V DC)	Output current (A)	Weight (kg)	Price each 1 to 5
ALIDRP240-24	85-264 / 120-370	24	10	1,2	227,29 €

Dimensions in mm

Our other products



ACLCHARJ
Hinge for aluminium profile, Adjusts in 2 directions



RFKfp
Stainless steel gearbox - accessories, Mounting bracket



VLBG
Lifting ring, Rotating



GMK17_BROSSE
Brush strip, Cone-shaped - brush



PPG
Indexing plunger with flange, With horizontal mounting flange



P40
Worm and wheel gear reducer, up to 18 Nm




HTD8M_50
HTD Heavy duty timing pulley, HTD8 Steel



RHTplss
High Temperature Castor, up to 200kg



PRES5HR
Manual workbench press, Force up to 500kg



B
Steel bevel gear, 1:1



PSG1
Spur gear - precision range, Pre-hardened Steel 35NCD6



CHM63-MOT
Asynchronous AC motorgearboxes 0.37 to 1.5kW, 0.37 to 1.5kW

Complementary products



DOG319
Motor-gearbox 12V and 24V DC, from 4 to 9 Nm



DOG258
Motor-gearbox 12V and 24V DC, from 12 to 15 Nm