

AT-type timing belt per metre



Pitch

AT5

AT10


Steel cored polyurethane

SINGLE-SIDED



Din 7721

- 2nd generation metric profile
- Transmits a greater load
- Pitch 5 or 10mm
- For linear movements
- Secured using rigid connecting plates
- Working temp. -20°C to +80°C
- Max. speed 40m/s
- Tolerance over length $\pm 0.8\text{mm}/1000\text{mm}$
- Efficiency: up to 98%
- Oil-resistant
- Low noise
- Resists stretching



For linear
positioning

Uses


- For reciprocating movements

Accessories



- Connecting plate AT.../P

Info.

- Min. length: 1000mm
- Supplied in multiples of 1 metre
- When ordering, add the length (L) and the width (l) to the part number (AT5M/L/l).
E.g.: AT5M/1000/16



Typical application



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Pitch	Price 1 to 5, per metre for width				
		10mm	16mm	25mm	32mm	50mm
AT5M	AT5	30,21 €	35,90 €	67,30 €	-	-
AT10M	AT10	-	-	58,04 €	74,08 €	82,33 €

Dimensions in mm


Our other products



PV2R
Adjustable suction-cup support,
Increased grip



RAGb
Cylindrical brush track,
For gentle
conveying and
handling



LAT4
4A motorised linear
actuator, 4 amperes



D19_D29
Compression springs
in metre length steel,
by the metre



EMS
Stainless steel knurled
thumb nut, Knurled



PF30
Worm and wheel gear
reducer, up to 8.80
Nm



GGP
Male wing knob,
Technopolymer with
stainless steel spindle



PPCss
Pad eye on mounting
plate squared,
Stainless steel



FF40
Offset spur gear
reducer, from 59 to
210 Nm



SSG2_304L
Stainless steel spur
gear, Stainless steel
304L



T10_30_AL
T type timing pulley,
Economy range - T10
aluminium



NRV
Orthogonal support
clamp, Orthogonal
support clamp

Complementary products



AT5P_AT10P
Connecting plate for
AT type timing belts,
AT5



AT5-10ECO
AT type timing pulley,
Economy range - AT5
aluminium



AT5-BAR
AT type tooth bar
stock, AT5



T5-10ECO
T type timing pulley,
Economy range - T5
aluminium