

# Hinge for aluminium profile

## ACL-CHARJ

## Adjusts in 2 directions






- Hinge that can be adjusted in 2 directions
- Allows precise positioning, both horizontally and vertically
- Materials:  
Plates – Moulded zinc  
Pin- stainless steel

### Advantages

- This hinge can be adjusted in both the X and Y planes thanks to use of serrated oblong holes and serrated washers

### Use

- Use M6 FHC screws (not supplied)  
See **FHC6-16/SS** (Vol 1, page 427)  
and **PRF-ECL-M6/SS** (Vol 5, page 323)



### DISCOUNTS

Qty	1+	50+	100+
Disc	Net	+5%	On request

Part N°	Load FA max (N)	Load FR max (N)	Weight (g)	Stock*	Price each 1 to 49
<b>Ajustable dans 2 directions</b>					
ACL-CHARJ60-76	1200	2200	190	-	26,92 €

## Our other products



DOMI120

Domino 120 adjustable slide, Slide DOMILINE 120 with counter and han...



PCS25ECO

Chain sprocket - steel, 6.35mm



ZDB

Machined plastic bevel gear , 2:1



RBGtc

Swivel castor with central hole, Steel - grey rubber



DOG316

Motor-gearbox 12V and 24V DC, from 1.5 to 2 Nm



PAL

Self locking counter nut, For axial locking



TBbutee

Axial thrust bearing, Steel balls



KB\_WW

Closed linear precision bearing, Economy range



INStool

Insertion tool for self tapping inserts, Insertion tool



CHAPAM

Weld-on hinge with flat end, Steel



DBL820

Idler for slat top chain, Ranges 820 and 815



PRF\_PL\_9090

Joining plate for aluminium profile, Joint plate - 90x90 mm

## Complementary products



FHCSS

Countersunk screw, Stainless steel A2 - DIN 7991



PRF\_ECL

Nut for aluminium profile, Stainless steel square nut with tab



PRF4545

Standard aluminium profile, 45 x 45 mm