

AT-type timing belt **per metre**



Pitch

Steel cored polyurethane


AT5
AT10

SINGLE-SIDED



Din 7721

- 2nd generation metric profile
- Transmits a greater load
- Pitch 5 or 10mm
- For linear movements
- Secured using rigid connecting plates
- Working temp. -20°C to +80°C
- Max. speed 40m/s
- Tolerance over length $\pm 0.8\text{mm}/1000\text{mm}$
- Efficiency: up to 98%
- Oil-resistant
- Low noise
- Resists stretching



For linear positioning

Uses


- For reciprocating movements

Accessories



- Connecting plate AT.../P

Info.

- Min. length: 1000mm
- Supplied in multiples of 1 metre
- When ordering, add the length (L) and the width (I) to the part number (AT5M/L/I).
- E.g.: AT5M/1000/16



Typical application



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Pitch	Price 1 to 5, per metre for width				
		10mm	16mm	25mm	32mm	50mm
AT5M	AT5	30,21 €	35,90 €	67,30 €	-	-
AT10M	AT10	-	-	58,04 €	74,08 €	82,33 €

Dimensions in mm

Our other products




RPC

Wheel, Polyamide



PTAF100-PAMF100

Articulated fixable
foot with pressed
base Ø100, Ø 100



H0

Crossed helical gear
crossed axis at 90°,
Machined plastic
(delrin)



CLR

Straight clevis,
Straight clevis for use
with a male clevis



GG1

Ground spur gear,
Heat treated steel



HK

Manual locking clamp,
Manual locking clamp
LRX



H0

Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



PRF_CHA

Hinge for aluminium
profile, Surface
mounting hinge



SUPCC

Self-centering
clamping hub steel,
With lock nut



BCH_SS

Mushroom headed
button, M3 to M8



SER69K

Quarter turn latch for
the food industry,
Stainless steel



BCM_CC

Modular cylindrical
brush, Horsehair
bristles

Complementary products



AT5P_AT10P

Connecting plate for
AT type timing belts,
AT10



AT10-32ECO

AT type timing pulley,
Economy range -
AT10 aluminium