

# Alu Connecting plate for AT type timing belts

For AT5M and AT10M timing belts

Pitch  
**AT5**  
**AT10**


- For linear movements
- Rigid connecting plate
- Pitches: 5 and 10mm
- For use with **AT5M** and **AT10M** belts supplied by the metre
- Material:  
Aluminium

## Uses


- For closing a belt or attaching one end of a belt to a frame



Until  
**-40%\*\***



Typical application



**✓ INCREASED STOCK**

## DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Pitch	B	L	H	E	F	G	Ød	A	Belt width	Stock*	Price each 1 to 5
AT5/25P	AT5	44	41,5	8	25	6	8,25	5,5	3,25	25	✓	18,30 €
AT10/25P	AT10	50	80,0	15	50	8	15,00	9,0	5,00	25	✓	25,86 €
AT10/32P	AT10	57	80,0	15	50	8	15,00	9,0	5,00	32	✓	27,39 €
AT10/50P	AT10	75	80,0	15	50	8	15,00	9,0	5,00	50	✓	30,43 €

Depending of availability - Dimensions in mm

## Our other products



PR550  
Stainless steel  
articulated foot Ø50,  
Ø 50



AC144  
Strike for toggle latch,  
22mm



SBF  
Sealed flange bearing  
unit for Food Industry,  
cover



PRF\_BP  
Doorstop for  
aluminium profile,  
Swing door stop



ALIDRP240  
24V DC power supply,  
10 A



PFL  
P-FLEX Coupling, Set  
screw



M1  
Worm and wheel set,  
Bronze



OPFL\_OPPM  
Numerical counter  
accessories,  
Operating knob



BAGSS  
Stainless steel  
Clamping collar,



S20  
Short housing for  
open linear bearing,



CHB  
Feet, For CHB gearbox



DOMI50  
Accessories, Fixing kit

## Complementary products



AT5M AT10M  
AT type timing belt  
per metre, AT5 Steel  
cored polyurethane