

Hinge for aluminium profile

ACL-CHARJ

Adjusts in 2 directions





- Hinge that can be adjusted in 2 directions
- Allows precise positioning, both horizontally and vertically
- Materials:
Plates – Moulded zinc
Pin- stainless steel

Advantages

- This hinge can be adjusted in both the X and Y planes thanks to use of serrated oblong holes and serrated washers

Use

- Use M6 FHC screws (not supplied)
See **FHC6-16/SS** (Vol 1, page 427)
and **PRF-ECL-M6/SS** (Vol 5, page 323)



DISCOUNTS

Qty	1+	50+	100+
Disc	Net	+5%	On request

Part N°	Load FA max (N)	Load FR max (N)	Weight (g)	Stock*	Price each 1 to 49
Ajustable dans 2 directions					
ACL-CHARJ60-76	1200	2200	190	-	26,92 €

Our other products




PTKFss
Fixable foot for the food industry, Stainless steel - 3-A standard




BAB
Hardened Stainless steel ball pin, Stainless steel hardened



AT5courroie
AT type timing belt, AT5 Steel cored polyurethane



M1
Worm and wheel set, Machined plastic (delrin)



CAB
Galvanised steel cable, Galvanised steel



CHAsb28
Roll of hinge without pin, Plastic hinge



CHT
Asynchronous AC motor 0.12 to 0.22kW, 0.12 to 0.22kW




SH1
Parallel axis helical gear, Machined plastic (delrin)



VPPTss
Stainless steel handwheel with handle, Stainless steel



PO
Pull handle - Multi-sector, Smooth hole



H0
Crossed helical gear crossed axis at 90°, Machined plastic



PRF_RR
Coupling bar for aluminium profile, Coupling bar

Complementary products



FHCSS
Countersunk screw, Stainless steel A2 - DIN 7991



PRF_ECL_
Nut for aluminium profile, Stainless steel square nut with tab



PRF4545
Standard aluminium profile, 45 x 45 mm