

Alu Connecting plate for AT type timing belts

For AT5M and AT10M timing belts

Pitch
AT5
AT10

- For linear movements

- Rigid connecting plate

- Pitches: 5 and 10mm

- For use with **AT5M** and **AT10M** belts supplied by the metre

- Material:


Aluminium

Uses


- For closing a belt or attaching one end of a belt to a frame



until
-40%**



Typical application



✓ **INCREASED STOCK**

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Pitch	B	L	H	E	F	G	Ød	A	Belt width	Stock*	Price each 1 to 5
AT5/25P	AT5	44	41,5	8	25	6	8,25	5,5	3,25	25	✓	18,30 €
AT10/25P	AT10	50	80,0	15	50	8	15,00	9,0	5,00	25	✓	25,86 €
AT10/32P	AT10	57	80,0	15	50	8	15,00	9,0	5,00	32	✓	27,39 €
AT10/50P	AT10	75	80,0	15	50	8	15,00	9,0	5,00	50	✓	30,43 €

Depending of availability - Dimensions in mm

Our other products



UCFL

Cast iron flanged bearing, Cast iron



CFUURSS

Cam follower stainless steel, Standard - stainless steel



PR85

Articulated foot Ø83, Ø 83



PSG2S

Spur gear - precision range, Stainless steel 316



VTH

Hexagonal headed bolts, Steel class 8.8



PDD

Spring plunger, With sensor adaptor



SLBS

Stainless steel indexing plunger, Stainless steel



VPRA_M

Handwheel with handle, Thermosetting plastic - galvanised steel hub



SCA_SS

Stainless steel flat cable clamp, Stainless steel



PSG125

Spur gear - precision range, Pre-hardened Steel 35NCD6



FF10

Offset spur gear reducer, from 0.78 to 3.70 Nm



PT821

Drive sprocket for slat top chain, Ranges 821 and 805

Complementary products



AT5M_AT10M

AT type timing belt per metre, AT10 Steel cored polyurethane