

Alu Connecting plate for AT type timing belts

For AT5M and AT10M timing belts

Pitch
AT5
AT10


- For linear movements
- Rigid connecting plate
- Pitches: 5 and 10mm
- For use with **AT5M** and **AT10M** belts supplied by the metre
- Material:
Aluminium

Uses


- For closing a belt or attaching one end of a belt to a frame



Until
-40%**



Typical application



INCREASED STOCK

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Pitch	B	L	H	E	F	G	Ød	A	Belt width	Stock*	Price each 1 to 5
AT5/25P	AT5	44	41,5	8	25	6	8,25	5,5	3,25	25	✓	18,30 €
AT10/25P	AT10	50	80,0	15	50	8	15,00	9,0	5,00	25	✓	25,86 €
AT10/32P	AT10	57	80,0	15	50	8	15,00	9,0	5,00	32	✓	27,39 €
AT10/50P	AT10	75	80,0	15	50	8	15,00	9,0	5,00	50	✓	30,43 €

Depending of availability - Dimensions in mm

Our other products



PHG05

Parallel axis helical gear - Precision range, 20NCD2 case hardened s...



CHA135

Screwed hinge, 135 degrees



VAP

Magnetic stud with central hole, With central hole



PSPT

Flexible tube handle, PVC



RJA00_28

Sealing strip, Clipping



gt64

Rotating bent lever, Common applications



PPS

Lifting ring, Universal threaded



SLB

Indexing plunger, stainless steel



CHA

Heavy duty plastic hinge, opens 180°.



VML

Stainless steel hexagonal headed



MFB

Flexible bellows coupling, Aluminium



GMC_GMK_BR

Guiding profile clamp, Flat or rounded

Complementary products



AT5M_AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane