


Steel or stainless steel

ADL_F

- ISO thread
- Material:
Black stamped steel
Stainless steel 316

Mounting

- For safe and correct assembly: Chamfer the hole into which the bolt will screw or use washers to ensure correct seating.
- Before assembly, clean the threads and corresponding tapped holes
- Screw lifting eye in fully
- The load should be lifted in the direction of the thread, +/- 20° and the pulling force should be along the axial plane of the eye.
- The use of these lifting eyes at an angle greater than 45° is not allowed.
- When the load to be lifted is aluminium, avoid leaving the eyes screwed in for long periods to avoid possible corrosion.



Steel eye bolt



Stainless steel eye bolt

Info.

*SWL: SAFE WORKING LOAD
The Safe Working Load is calculated by dividing the breaking Strength by a factor of safety of 5.

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

Part number	Ød	H	ØD1	ØD2	ØG	E	ØS	CMU (kg)	CMU at 45° (kg)	Weight (kg)	Stock*	Price each 1 to 5
Steel eye bolt												
ADL-6F	M6	36	36	20	22	9	9	90	60	0,060	✓	2,13 €
ADL-8F	M8	36	36	20	21	11	9	140	95	0,060	✓	2,16 €
ADL-10F	M10	45	45	25	26	10	10	230	170	0,100	✓	2,57 €
ADL-12F	M12	52	55	29	31	11	12	340	240	0,160	✓	3,45 €
ADL-16F	M16	62	63	34	34	15	14	700	500	0,240	✓	4,83 €
ADL-20F	M20	71	72	39	40	17	16	1200	830	0,360	✓	7,54 €
ADL-24F	M24	89	90	48	49	22	21	1800	1270	0,715	-	13,37 €
ADL-30F	M30	109	108	60	65	25	24	3200	2300	1,400	-	26,09 €
ADL-36F	M36	137	127	69	81	38	31	4600	3300	2,300	-	45,25 €
ADL-42F	M42	147	144	80	85	35	32	6300	4500	3,500	-	88,71 €
ADL-48F	M48	185	170	88	102	45	41	8600	6100	5,670	-	143,01 €

Stainless steel eye bolt

ADL-6F/SS	M6	-	35	19	20	9	9	180	-	0,055	✓	6,77 €
ADL-8F/SS	M8	-	36	19	20	10	8	300	-	0,050	✓	7,63 €
ADL-10F/SS	M10	-	45	24	24	11	9	500	-	0,090	✓	12,66 €
ADL-12F/SS	M12	-	53	29	29	13	12	800	-	0,155	✓	17,67 €
ADL-14F/SS	M14	-	54	30	30	11	12	1100	-	0,165	-	20,18 €
ADL-16F/SS	M16	-	63	34	35	15	14	1500	-	0,250	-	21,61 €
ADL-20F/SS	M20	-	72	40	40	15	16	2400	-	0,360	✓	42,73 €
ADL-24F/SS	M24	-	90	50	50	20	20	3600	-	0,720	-	76,30 €

*Depending on availability - Dimensions in mm

Our other products



GARQT
Quarter turn lock pin for clamping, Quarter turn



CAP815
Slim slat top chain stainless steel, Narrow range 815



RT61ss
Self-centering locking Assembly, Medium/low torque




ACM_TRI
Manual bonnet fastener, Black rubber fastener



SMS
Spiral bevel gear, 1:1



ACLLPP
Latch for aluminium profile, Spring operated latch




QNJ
Single row cylindrical roller bearing, Single flange on inner ring



PR882
Idler sprocket for slat top chain, Range 882



GPB
Threaded spherical knob, With brass



CHB
Worm and wheel gear reducer, up to 22 Nm



LRR
Catch-plate for latch, Catch-plate



NTMbr
Set screw brass tip, Brass-point

Complementary products



ADL_F
Female eye bolt conforms to DIN582, Stainless steel



ADL_M
Male eye bolt conforms to DIN580, Steel



VRM
Female swivelling lifting rings, Female swivelling



VRSF
Male swivelling lifting ring, Male swivelling