

# Ball lock pins lockable



## BABv

## With simple grip

- Lockable version prevents **unintentional loosening of the connection**
- The balls can only be unlocked using a key
- Materials :
  - Handle: red thermoplastic (RAL3020)
  - Shaft: 303 stainless steel
  - Components: stainless steel
  - Lock: Die cast zinc
  - Key: Zinc-plated steel
- For H11 bore


### Advantages

- Press to unlock
- Quick and easy to assemble, block, adjust, change and stop
- Simply and quickly released when performing repetitive operations
- Corrosion resistant
- Resists high loads
- Ergonomic handle
- Can be fitted with **CDR** retaining cable (**tome 1 p.35**)

### Infos

- Shear strength to DIN 50141
- The push-button lock has identical locking. All cylinders can be opened with the same key. Lockable locking pins are supplied with two keys





## DISCOUNTS

Qty	1+	6+	10+
Disc. List	-5%	-5%	On request

Part Number	B	ØD	ØD1	ØD2	ØD3	L	L1	L2	L3	L5	Double shear resistance kN min	Price each 1 to 5
BAB8-20/V/R	33	45,9	8	9,5	20	20	7,8	49,5	41,3	27,8	38	43,94 €
BAB8-25/V/R	33	45,9	8	9,5	20	25	7,8	49,5	41,3	32,8	38	43,94 €
BAB8-30/V/R	33	45,9	8	9,5	20	30	7,8	49,5	41,3	37,8	38	47,10 €
BAB8-35/V/R	33	45,9	8	9,5	20	35	7,8	49,5	41,3	42,8	38	47,10 €
BAB8-40/V/R	33	45,9	8	9,5	20	40	7,8	49,5	41,3	47,8	38	47,10 €
BAB8-45/V/R	33	45,9	8	9,5	20	45	7,8	49,5	41,3	52,8	38	47,10 €
BAB8-50/V/R	33	45,9	8	9,5	20	50	7,8	49,5	41,3	57,8	38	47,10 €
BAB10-20/V/R	33	45,9	10	12,0	20	20	8,9	49,5	41,3	28,9	60	61,41 €
BAB10-25/V/R	33	45,9	10	12,0	20	25	8,9	49,5	41,3	33,9	60	61,41 €
BAB10-30/V/R	33	45,9	10	12,0	20	30	8,9	49,5	41,3	38,9	60	64,08 €
BAB10-35/V/R	33	45,9	10	12,0	20	35	8,9	49,5	41,3	43,9	60	64,08 €
BAB10-40/V/R	33	45,9	10	12,0	20	40	8,9	49,5	41,3	48,9	60	64,08 €
BAB10-45/V/R	33	45,9	10	12,0	20	45	8,9	49,5	41,3	53,9	60	64,08 €
BAB10-50/V/R	33	45,9	10	12,0	20	50	8,9	49,5	41,3	58,9	60	64,08 €
BAB10-60/V/R	33	45,9	10	12,0	20	60	8,9	49,5	41,3	68,9	60	67,40 €
BAB12-25/V/R	33	45,9	12	14,5	20	25	9,9	49,5	41,3	34,9	86	55,18 €
BAB12-30/V/R	33	45,9	12	14,5	20	30	9,9	49,5	41,3	39,9	86	58,16 €
BAB12-35/V/R	33	45,9	12	14,5	20	35	9,9	49,5	41,3	44,9	86	58,16 €
BAB12-40/V/R	33	45,9	12	14,5	20	40	9,9	49,5	41,3	49,9	86	58,16 €
BAB12-45/V/R	33	45,9	12	14,5	20	45	9,9	49,5	41,3	54,9	86	58,16 €
BAB12-50/V/R	33	45,9	12	14,5	20	50	9,9	49,5	41,3	59,9	86	58,16 €
BAB12-60/V/R	33	45,9	12	14,5	20	60	9,9	49,5	41,3	69,9	86	61,14 €
BAB12-70/V/R	33	45,9	12	14,5	20	70	9,9	49,5	41,3	79,9	86	61,14 €
BAB12-80/V/R	33	45,9	12	14,5	20	80	9,9	49,5	41,3	89,9	86	63,78 €
BAB16-30/V/R	33	45,9	16	19	20	30	13,1	49,5	41,3	43,1	153	81,76 €
BAB16-35/V/R	33	45,9	16	19	20	35	13,1	49,5	41,3	48,1	153	83,07 €
BAB16-40/V/R	33	45,9	16	19	20	40	13,1	49,5	41,3	53,1	153	83,07 €
BAB16-45/V/R	33	45,9	16	19	20	45	13,1	49,5	41,3	58,1	153	83,07 €
BAB16-50/V/R	33	45,9	16	19	20	50	13,1	49,5	41,3	63,1	153	83,07 €
BAB16-60/V/R	33	45,9	16	19	20	60	13,1	49,5	41,3	73,1	153	88,27 €
BAB16-70/V/R	33	45,9	16	19	20	70	13,1	49,5	41,3	83,1	153	88,27 €
BAB16-80/V/R	33	45,9	16	19	20	80	13,1	49,5	41,3	93,1	153	93,43 €

Dimensions in mm

## Our other products



SCA\_SS

Stainless steel flat cable clamp, Stainless steel



PSG08S

Spur gear - precision range, Stainless steel 316



MAX26

Motor-gearbox 12V and 24V DC, from 0,075 to 0,6Nm



WS20

Drylin® W rail, Rail



T25-6ECO

T type timing pulley, Economy range - T2.5 aluminium



INS100

Self tapping inserts-coarse thread, Coarse thread



SH1

Parallel axis helical gear, Steel 20NC2



BOXdhx

Boxed set of threaded dowel pins DIN7979D, Boxed set - extractable D...



F7-SF-SM

Multifunction display, Mounting bracket for front mounting




HLA19

Right angle spiro bevel gearbox, Up to 43Nm



CHM50

Worm and wheel gear reducer, up to 107 Nm



PRZ

Wear strip for slat top chain, Z profile to be filled

## Complementary products



BABTV

Ball lock pins lockable, Stainless steel



BABreceptacle

Ball pin socket, Socket



BABFCFO

Ball pin socket, Mounting collar with a round flange



BABFCFO

Ball pin socket, Mounting collar with a oval flange