



Single or two part assembly

BAG1ss
BAG2ss

- Solid fixing onto any type of shaft
- Do not separate the two pieces
- Materials:
Clamp + screw: stainless steel
Screw: steel alloy
- 2-part clamps offer a 20% stronger fixing
- Dimensions ØD and L are given as an indication only and are subject to change



Typical application

DISCOUNTS

Qty	1+	5+	10+	25+	50+
Disc	List	-6%	-12%	-18%	On request

Part number		ØA	ØD	L	Screw	Stock*	Stock*	Price each 1 to 4	
1 part	2 parts					1 part	2 parts	1 part	2 parts
BAG1-004/SS	BAG2-004/SS	4	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-005/SS	BAG2-005/SS	5	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-006/SS	BAG2-006/SS	6	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-008/SS	BAG2-008/SS	8	18	9	M3 x 8	✓	✓	9,11 €	10,67 €
BAG1-010/SS	BAG2-010/SS	10	24	9	M3 x 10	✓	✓	11,27 €	13,31 €
BAG1-012/SS	BAG2-012/SS	12	28	11	M4 x 12	✓	✓	11,64 €	13,81 €
BAG1-015/SS	BAG2-015/SS	15	34	13	M5 x 16	✓	✓	13,93 €	16,92 €
BAG1-016/SS	BAG2-016/SS	16	34	13	M5 x 16	✓	✓	13,93 €	16,92 €
BAG1-018/SS	BAG2-018/SS	18	36	13	M5 x 16	✓	✓	15,92 €	19,01 €
BAG1-020/SS	BAG2-020/SS	20	40	15	M6 x 16	✓	✓	19,40 €	20,24 €
BAG1-025/SS	BAG2-025/SS	25	45	15	M6 x 16	✓	✓	21,44 €	23,01 €
BAG1-030/SS	BAG2-030/SS	30	54	15	M6 x 18	✓	✓	24,76 €	27,59 €
BAG1-040/SS	BAG2-040/SS	40	60	15	M6 x 18	✓	✓	30,93 €	38,38 €
BAG1-050/SS	BAG2-050/SS	50	78	19	M8 x 25	✓	✓	58,29 €	84,96 €
BAG1-055/SS	BAG2-055/SS	55	90	16	M8 x 20	-	-	84,02 €	88,99 €
BAG1-060/SS	BAG2-060/SS	60	100	16	M8 x 20	-	✓	96,82 €	101,91 €
BAG1-070/SS	BAG2-070/SS	70	110	20	M10 x 25	-	-	107,85 €	113,61 €
BAG1-075/SS	BAG2-075/SS	75	125	20	M10 x 25	-	-	138,32 €	144,27 €
BAG1-080/SS	BAG2-080/SS	80	125	20	M10 x 25	-	-	131,65 €	137,52 €

*Depending on availability - Dimensions in mm

Our other products



T5P_T10P

Connecting plate for T type timing belts, T5



DOG316

Motor-gearbox 12V and 24V DC, from 1.5 to 2 Nm



RTK

BoWex® curved tooth gear coupling, Nylon and steel



ACLLPP

Latch for aluminium profile, Spring operated latch



BLHB60

Right angled gearbox, bored shafts, up to 70 Nm



CFF

Female rod ends DIN ISO12240-4, Steel / bronze



HK

Manual locking clamp, Manual locking clamp T



SVG

Adjustable latch clamp with strike plate, Stroke from 174mm to 190mm



HRV

V-rail guidance Simple Select® system, Rail with



PRF_SDD_1820

Support for Ø18 or Ø20mm Prox detector, Ø18 and



PLM-20SC

Cylindrical magnet, Cylindrical magnet



PTRSS

Idler chain sprocket, For hostile environments

Complementary products



BAGSS

Stainless steel Clamping collar, Stainless steel



BAG

Steel Clamping collar, Steel