


- Suitable for linear (push/pull) operations
- Material:
Stainless steel 303
Finish: Electrolytically polish

Economical range



DISCOUNTS

Qty	1+	10+	20+	50+
Disc. List	-10%	-20%	On request	

Part number	ØD	ØD1	ØD2	H	H1	T	Stock*	Price each 1 to 9
BCH3-18/SS	M3	18	10	18	8,6	7,5	✓	8,99 €
BCH4-21/SS	M4	21	12	21	10,0	10,0	✓	9,84 €
BCH5-21/SS	M5	21	12	21	10,0	12,5	✓	10,59 €
BCH6-25/SS	M6	25	14	25	12,0	12,0	✓	11,78 €
BCH8-33/SS	M8	33	18	33	16,0	16,0	✓	17,24 €

*Depending on availability - Dimensions in mm

Our other products



BEF
Bearing housing for miniature ballscrew, Bearing housing




VDSQCB
Sliding lock adjustment system, Blocking wedge




HLC28
Right angle spiro bevel gearbox, Up to 182Nm



P20
Worm and wheel gear reducer, up to 5 Nm



PM2
Worm and wheel set, Machined plastic (delrin)




LAT4
4A motorised linear actuator, 4 amperes



PDD
Actuating plunger, Non-rotating detector shaft



PRF-P
Aluminium profile feet support, For feet or casters



RPP14
RPP heavy duty timing belt, RPP14



PSG125HC
Skive hobbled spur gears - precision range, Case hardened



BPHF
Ball transfer unit push fit, Heavy



T39_T49
Extension spring in metre length steel, by the metre

Complementary products