


- Suitable for linear (push/pull) operations
- Material:
Stainless steel 303
Finish: Electrolytically polish

Economical range



DISCOUNTS

Qty	1+	10+	20+	50+
Disc. List	-10%	-20%	On request	

Part number	ØD	ØD1	ØD2	H	H1	T	Stock*	Price each 1 to 9
BCH3-18/SS	M3	18	10	18	8,6	7,5	✓	8,99 €
BCH4-21/SS	M4	21	12	21	10,0	10,0	✓	9,84 €
BCH5-21/SS	M5	21	12	21	10,0	12,5	✓	10,59 €
BCH6-25/SS	M6	25	14	25	12,0	12,0	✓	11,78 €
BCH8-33/SS	M8	33	18	33	16,0	16,0	✓	17,24 €

*Depending on availability - Dimensions in mm

Our other products




CHB

Worm and wheel gear reducer, up to 22 Nm



RUR

Wheel, Polyurethane - Aluminium rim (Free running)



AWMP

Aluminium shaft for linear guide, Aluminium



SHA_PTR

Handwheel with folding handle, Polyamide



SLH

Horizontal toggle clamp, Horizontal Lever Clamp - steel



RAS

90° ball and socket joints DIN71802, Stainless steel



RCX-6

Spherical tilt washer - DIN6319, convex




CHMR110

Worm and wheel gear reducer, up to 980 Nm



BPPL

Assembly tool for carrier ball, Mounting




EPRF

High helix leadscrew, Flanged nut - up to



ECF

Well nut, Chloroprene elastomer



T0

Torsion spring, Stainless steel

Complementary products