



AT-type timing belt


Steel cored polyurethane

Pitch AT10

- 2nd generation metric profile
- Transmits a greater torque
- Pitch 10mm
- Working temp. -30°C to +80°C
- Max. speed 40m/s
- Efficiency: up to 98%
- Oil-resistant
- Low noise
- Resists stretching

Info.

- When ordering, add the width to the part number
- E.g.: AT5/525/25




DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Length	No. of teeth	Price each 1 to 5 for widths		
			25mm	32mm	50mm
AT10/500	500	50	51.72 €	65.26 €	95.97 €
AT10/560	560	56	54.51 €	-	102.34 €
AT10/600	600	60	56.09 €	71.63 €	104.73 €
AT10/610	610	61	56.50 €	72.05 €	105.49 €
AT10/660	660	60	60.11 €	76.82 €	112.29 €
AT10/700	700	70	62.47 €	80.40 €	117.05 €
AT10/730	730	73	64.45 €	83.59 €	120.64 €
AT10/780	780	78	67.66 €	87.19 €	127.42 €
AT10/800	800	80	69.63 €	88.78 €	129.03 €
AT10/840	840	84	72.85 €	93.15 €	135.80 €
AT10/890	890	89	78.03 €	100.31 €	146.17 €
AT10/920	920	92	81.20 €	105.11 €	153.34 €
AT10/960	960	96	86.40 €	112.29 €	162.10 €
AT10/980	980	98	89.15 €	113.49 €	170.46 €
AT10/1000	1000	100	91.15 €	116.67 €	173.25 €
AT10/1010	1010	101	91.95 €	117.05 €	174.43 €
AT10/1050	1050	105	93.56 €	120.27 €	178.03 €
AT10/1080	1080	108	94.75 €	121.84 €	179.63 €
AT10/1100	1100	110	96.75 €	123.84 €	183.21 €
AT10/1150	1150	115	99.12 €	127.42 €	188.77 €
AT10/1200	1200	120	101.51 €	130.98 €	193.57 €
AT10/1210	1210	121	101.94 €	131.79 €	194.76 €
AT10/1250	1250	125	104.73 €	134.60 €	198.76 €
AT10/1280	1280	128	105.49 €	136.60 €	201.13 €
AT10/1300	1300	130	107.10 €	138.18 €	203.52 €
AT10/1320	1320	132	108.70 €	140.18 €	207.10 €
AT10/1350	1350	135	111.09 €	142.95 €	211.89 €
AT10/1360	1360	136	112.29 €	144.16 €	213.90 €
AT10/1400	1400	140	115.47 €	149.74 €	220.68 €
AT10/1480	1480	148	121.84 €	158.48 €	233.82 €
AT10/1500	1500	150	123.04 €	160.50 €	236.60 €
AT10/1600	1600	160	130.98 €	171.23 €	252.56 €
AT10/1700	1700	170	139.38 €	181.61 €	268.88 €
AT10/1720	1720	172	141.37 €	183.21 €	271.64 €
AT10/1800	1800	180	147.35 €	192.36 €	284.41 €
AT10/1860	1860	186	152.14 €	198.35 €	292.78 €
AT10/1940	1940	194	159.30 €	209.12 €	309.54 €

Dimensions in mm

Our other products



GPLny

Brush, nylon



5H2

Parallel axis helical gear, Machined plastic (delrin)



BSM

Spring plunger with internal hexagonal socket, stainless steel 303 b...




PMC48_M8

Anti-vibration machine mount, Oval base plate



BDP1R

Adjustable support arm, Single clamp



TR

Spur round rack, Stainless steel - module 0,25-1,5



BPHT

Ball transfer unit bolt fitting, Heavy



PDR-RD

Mounting feet with integrated castors, Offset castor



PR881

Idler sprocket for slat top chain, Range 881



ACL-PR

Joining plate for aluminium profile,



VB

Small 6 lobe threaded handle - female,



G0

Steel spur gear, Steel 20NCD2

Complementary products



GTC

Belt tensioner, For standard applications



AT10-32ECO

AT type timing pulley, Economy range - AT10 aluminium