

AT-type timing belt **per metre**



Pitch

AT5

AT10


Steel cored polyurethane

SINGLE-SIDED



Din 7721

- 2nd generation metric profile
- Transmits a greater load
- Pitch 5 or 10mm
- For linear movements
- Secured using rigid connecting plates
- Working temp. -20°C to +80°C
- Max. speed 40m/s
- Tolerance over length $\pm 0.8\text{mm}/1000\text{mm}$
- Efficiency: up to 98%
- Oil-resistant
- Low noise
- Resists stretching



For linear positioning

Uses


- For reciprocating movements

Accessories



- Connecting plate AT.../P

Info.

- Min. length: 1000mm
- Supplied in multiples of 1 metre
- When ordering, add the length (L) and the width (l) to the part number (AT5M/L/l).
- E.g.: AT5M/1000/16



Typical application



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Pitch	Price 1 to 5, per metre for width				
		10mm	16mm	25mm	32mm	50mm
AT5M	AT5	30,21 €	35,90 €	67,30 €	-	-
AT10M	AT10	-	-	58,04 €	74,08 €	82,33 €

Dimensions in mm

Our other products



SH0

Parallel axis helical gear, Machined plastic (delrin)



ATZYSS

Stainless steel diabolo shaped elasto mount, Stainless steel



JCDss

Double universal joint - Stainless steel, Low duty



NT91

Spur gear coaxial gearbox, from 10 to 35 Nm - Inline




CHTRB

Single and dual output gearboxes, Up to 87,3 Nm



H0

Crossed helical gear crossed axis at 90°, Steel 20NCD2



KGS

Ballscrew, supplied by the metre, Rolled ballscrew, per metre



BPMc

Stainless steel slotted spring plunger with ceramic ball tip, 303 St...



RJA10_03

Sealing strip, Clipping



CLB_M

Die cast zinc clamping lever - female, Zamak



SLH-M

Nut for toggle clamp, Round ended nut for SLH/SLV clamp



PLC_PLT

Magnetic stud with central hole, With central hole

Complementary products



AT5P_AT10P

Connecting plate for AT type timing belts, AT10



AT10-50ECO

AT type timing pulley, Economy range - AT10 aluminium