

# AT-type timing belt **per metre**



Pitch

Steel cored polyurethane


**AT5**  
**AT10**

SINGLE-SIDED



Din 7721

- 2nd generation metric profile
- Transmits a greater load
- Pitch 5 or 10mm
- For linear movements
- Secured using rigid connecting plates
- Working temp. -20°C to +80°C
- Max. speed 40m/s
- Tolerance over length ±0.8mm/1000mm
- Efficiency: up to 98%
- Oil-resistant
- Low noise
- Resists stretching



For linear positioning

## Uses


- For reciprocating movements

## Accessories



- Connecting plate AT.../P

## Info.

- Min. length: 1000mm
- Supplied in multiples of 1 metre
- When ordering, add the length (L) and the width (I) to the part number (AT5M/L/I).
- E.g.: AT5M/1000/16



Typical application



## DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Pitch	Price 1 to 5, per metre for width				
		10mm	16mm	25mm	32mm	50mm
AT5M	AT5	30,21 €	35,90 €	67,30 €	-	-
AT10M	AT10	-	-	58,04 €	74,08 €	82,33 €

Dimensions in mm

## Our other products



CHAC4040NP

Square hinge with riveted pin, not drilled, Square with riveted pin,...



CABtool

Fitting cable tools, Crimping tools



BOX-TOR-D

Box set of Nitrile O-rings in nitrile, 18.00 x 2.00mm to 50.00 x 5.00



MCL

Cylindrical threaded sleeve, Cylindrical - stainless steel



BOX-TOR-MAX

Box set of Nitrile O-rings in nitrile, 2.90 x 1.78mm to 82.14 x 3.53



FF10

Offset spur gear reducer, from 0.78 to 3.70 Nm



CHAsb28

Roll of hinge without pin, Plastic hinge



MSP3815

Masterplate® glueable insert rectangular, rectangular with



WW10

Drylin® W slide, slide assembly




RAM35

Manual bevel gearbox, Bevel



PTA80

Articulated levelling foot, pressed base



GPLso

Brush, silk

## Complementary products



AT5P\_AT10P

Connecting plate for AT type timing belts, AT10



AT10-32ECO

AT type timing pulley, Economy range - AT10 aluminium