

AT-type timing belt **per metre**



Pitch

AT5

AT10


Steel cored polyurethane

SINGLE-SIDED



Din 7721

- 2nd generation metric profile
- Transmits a greater load
- Pitch 5 or 10mm
- For linear movements
- Secured using rigid connecting plates
- Working temp. -20°C to +80°C
- Max. speed 40m/s
- Tolerance over length $\pm 0.8\text{mm}/1000\text{mm}$
- Efficiency: up to 98%
- Oil-resistant
- Low noise
- Resists stretching



For linear positioning

Uses


- For reciprocating movements

Accessories



- Connecting plate AT.../P

Info.

- Min. length: 1000mm
- Supplied in multiples of 1 metre
- When ordering, add the length (L) and the width (I) to the part number (AT5M/L/I).
- E.g.: AT5M/1000/16



Typical application



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Pitch	Price 1 to 5, per metre for width				
		10mm	16mm	25mm	32mm	50mm
AT5M	AT5	30,21 €	35,90 €	67,30 €	-	-
AT10M	AT10	-	-	58,04 €	74,08 €	82,33 €

Dimensions in mm

Our other products



MLY

Bow shackle with eye bolt, Steel



PT880

Drive sprocket for slat top chain, Range 880



GE32

Sprung toggle latch with connecting link, Standard



AT5P_AT10P

Connecting plate for AT type timing belts, AT10



CLQassortiment

Assorted feeler strips, Assorted feeler strips



MPB

Hexagonal spacer, Brass




PHT

Pull handle, Up to 250 °C



SERB

Cam latch, Cam latch



BOX-TOR-TOOL

Box set of tool for Nitrile O-rings, Extraction tools



BOXINS300

Box set of self tapping inserts, Boxed set - For hard materials



PRF_CH

Cable-carrier chain for aluminium profile, Supplied in metre



LRX

Linear roller slide, Chariot - from 9410 N to 101000 N

Complementary products



AT5P_AT10P

Connecting plate for AT type timing belts, AT5



AT5-10ECO

AT type timing pulley, Economy range - AT5 aluminium



AT5-BAR

AT type tooth bar stock, AT5



T5-10ECO

T type timing pulley, Economy range - T5 aluminium