

Alu Connecting plate for AT type timing belts

For AT5M and AT10M timing belts

Pitch
AT5
AT10


- For linear movements
- Rigid connecting plate
- Pitches: 5 and 10mm
- For use with **AT5M** and **AT10M** belts supplied by the metre
- Material:
Aluminium

Uses


- For closing a belt or attaching one end of a belt to a frame



Until
-40%**



Typical application



✓ INCREASED STOCK

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request


Part number	Pitch	B	L	H	E	F	G	Ød	A	Belt width	Stock*	Price each 1 to 5
AT5/25P	AT5	44	41,5	8	25	6	8,25	5,5	3,25	25	✓	18,30 €
AT10/25P	AT10	50	80,0	15	50	8	15,00	9,0	5,00	25	✓	25,86 €
AT10/32P	AT10	57	80,0	15	50	8	15,00	9,0	5,00	32	✓	27,39 €
AT10/50P	AT10	75	80,0	15	50	8	15,00	9,0	5,00	50	✓	30,43 €

Depending of availability - Dimensions in mm

Our other products



Backlash free coupling Gerwah®, from 1.2 to 450Nm



High rigidity linear slide, Chariot - from 9320 N to 71300 N



Stainless/Polymer pillow block bearing, Polymer and stainless steel



Tightening washer - DIN6340, Steel



Worm and wheel gear reducer, up to 57 Nm



Square hinge with riveted pin, drilled, Square with riveted pin, dri...



Crossed helical gear crossed axis at 90°, Steel 20NCD2




AT type timing pulley, Economy range - AT10 aluminium



Strike for toggle latch, 25.5mm



Potentiometer,



Knurled knob - male, Knurled



Accessories, Clamping lever

Complementary products



AT type timing belt per metre, AT5 Steel cored polyurethane