

Alu Connecting plate for AT type timing belts

For AT5M and AT10M timing belts

Pitch
AT5
AT10


- For linear movements
- Rigid connecting plate
- Pitches: 5 and 10mm
- For use with **AT5M** and **AT10M** belts supplied by the metre
- Material:
Aluminium

Uses


- For closing a belt or attaching one end of a belt to a frame



Until
-40%**



Typical application



✓ INCREASED STOCK

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request


Part number	Pitch	B	L	H	E	F	G	Ød	A	Belt width	Stock*	Price each 1 to 5
AT5/25P	AT5	44	41,5	8	25	6	8,25	5,5	3,25	25	✓	18,30 €
AT10/25P	AT10	50	80,0	15	50	8	15,00	9,0	5,00	25	✓	25,86 €
AT10/32P	AT10	57	80,0	15	50	8	15,00	9,0	5,00	32	✓	27,39 €
AT10/50P	AT10	75	80,0	15	50	8	15,00	9,0	5,00	50	✓	30,43 €

Depending of availability - Dimensions in mm

Our other products



MRA_SS
Stainless steel Quick link, Stainless steel



CHB
Worm and wheel gear reducer, up to 22 Nm



ADL_F
Female eye bolt conforms to DIN582, Stainless steel



PRF_BV
Screw block, Panel addition and fastening



BABFCFO
Ball pin socket, Mounting collar with a round flange



TFR
Rigid manual tensioner, Fixed



BPM
Slotted spring plunger with ball tip, Stainless steel 303



PO
Pull handle - Multi-sector, Smooth hole



PSG2S
Spur gear - precision range, Stainless steel 316



GE_ES_2RS
Spherical bushing, Steel / steel with seals



DOMI120
Accessories, Turntable



EKGS
Backlash free coupling Gerwah®, from 0.5 to 35Nm

Complementary products



AT5M AT10M
AT type timing belt per metre, AT10 Steel cored polyurethane