

Alu Connecting plate for AT type timing belts

For AT5M and AT10M timing belts

Pitch
AT5
AT10


- For linear movements
- Rigid connecting plate
- Pitches: 5 and 10mm
- For use with **AT5M** and **AT10M** belts supplied by the metre
- Material:
Aluminium

Uses


- For closing a belt or attaching one end of a belt to a frame



Until
-40%**



Typical application



INCREASED STOCK

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	Pitch	B	L	H	E	F	G	Ød	A	Belt width	Stock*	Price each 1 to 5
AT5/25P	AT5	44	41,5	8	25	6	8,25	5,5	3,25	25	✓	18,30 €
AT10/25P	AT10	50	80,0	15	50	8	15,00	9,0	5,00	25	✓	25,86 €
AT10/32P	AT10	57	80,0	15	50	8	15,00	9,0	5,00	32	✓	27,39 €
AT10/50P	AT10	75	80,0	15	50	8	15,00	9,0	5,00	50	✓	30,43 €

Depending of availability - Dimensions in mm

Our other products



PW_PWG05
Worm - precision range, Stainless steel



UTKswrr
V shaped channel UtiliTrak®, V rail



T2,5-BAR
T type tooth bar stock, T2.5



PRS100
Stainless steel articulated foot Ø100, Ø 100



PITA
Locking bolt, with T handle



BCA
Steel splined collar, Steel



ACL-FPA
Panel mounting block for aluminium structures, Support block



SCA_SS
Stainless steel flat cable clamp, Stainless steel



PT880
Drive sprocket for slat top chain, Range 880



BSM
Spring plunger with internal hexagonal



TAC
Rigging screw (hook/eye), Steel



PAL
Self locking counter nut, For axial locking

Complementary products



AT5M AT10M
AT type timing belt per metre, AT10 Steel cored polyurethane