

# Miniature indexing button

For reduced spaces

BIM

Miniature

- Particularly suitable for screwing into thin-walled parts.
- Works well in reduced spaces
- Non-removable spaces
- Materials:  
Head - matt thermoplastic  
Body - galvanised steel or 303 stainless steel  
Pin - 303 stainless steel





## Assembly

- Screw in as far as possible, then pull on the button to reveal the hexagonal nut for final assembly.

## Operation

- For the locking version, the button is pulled and then turned 90°C where it is retained in a notch.
- Working temperature range -30°C to 80°C



## DISCOUNTS

Qty	1+	6+	20+
Disc	List	-10%	On request

Part number	ØD1	ØD2	L1	ØD3	ØD4	L2	L3	L4	SW	F1 (N)	F2 (N)	Weight (g)	Stock*	Price each 1 to 5
<b>Non-locking version</b>														
BIM4-8-26.5	4	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	✓	7,99 €
BIM5-8-26.5	5	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	✓	8,21 €
BIM6-10-34	6	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	25	✓	9,65 €
BIM7-10-34	7	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	26	-	10,13 €
<b>Locking version</b>														
BIM4-8-26.5/LOK	4	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	13	✓	7,99 €
BIM5-8-26.5/LOK	5	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	-	8,21 €
BIM6-10-34/LOK	6	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	24	-	9,65 €
BIM7-10-34/LOK	7	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	25	-	10,13 €

Dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

137

## Our other products



BPLF

Ball transfer unit light duty, Light



PHG05

Parallel axis helical gear - Precision range, 20NCD2 case hardened s...



PT821

Drive sprocket for slat top chain, Ranges 821 and 805



QNU

Single row cylindrical roller bearing, Free inner ring



BTE

Universal tension arm, For standard applications



MEB

Moulded plastic bevel gear (nylon), 1:1



SLB

Indexing plunger, stainless steel



PSP

Support profile, Panel support



SCR

Suction cup threaded insert, Adaptator for insert



PLB

Cylindrical spacer, Brass



PX

Optional output shaft stainless steel, P gearboxes double



RPP

Connecting plate for RPP type timing belts, RPPB

## Complementary products



BIMSS

Indexing plunger mini, miniature - Stainless steel



PPD

Indexing plunger for sheets, For sheet metal



PPF

Indexing plunger with flange, with drilled flange



SLBW

Indexing plunger, weldable, Weldable - Steel