

Miniature indexing button

For reduced spaces

BIM

Miniature

- Particularly suitable for screwing into thin-walled parts.
- Works well in reduced spaces
- Non-removable spaces
- Materials:
Head - matt thermoplastic
Body - galvanised steel or 303 stainless steel
Pin - 303 stainless steel





Assembly

- Screw in as far as possible, then pull on the button to reveal the hexagonal nut for final assembly.

Operation

- For the locking version, the button is pulled and then turned 90°C where it is retained in a notch.
- Working temperature range -30°C to 80°C



DISCOUNTS

Qty	1+	6+	20+
Disc	List	-10%	On request

Part number	ØD1	ØD2	L1	ØD3	ØD4	L2	L3	L4	SW	F1 (N)	F2 (N)	Weight (g)	Stock*	Price each 1 to 5
Non-locking version														
BIM4-8-26.5	4	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	✓	7,99 €
BIM5-8-26.5	5	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	✓	8,21 €
BIM6-10-34	6	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	25	✓	9,65 €
BIM7-10-34	7	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	26	-	10,13 €
Locking version														
BIM4-8-26.5/LOK	4	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	13	✓	7,99 €
BIM5-8-26.5/LOK	5	M8x0,75	26,5	21,0	15,0	5	5	3,5	10	4,5	12	14	-	8,21 €
BIM6-10-34/LOK	6	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	24	-	9,65 €
BIM7-10-34/LOK	7	M10x1	34	25,0	18,0	7	7	4,5	12	5	18	25	-	10,13 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

137

Our other products




BPLE

Ball transfer unit push fit, Light



CHB

Reaction arm, CHB gear reducers reaction arm



H2

Crossed helical gear crossed axis at 90°, Machined plastic (delrin)



LRR-53

Spring loaded latch, Spring return latch - stainless steel



VEL

Self-gripping cable strip, electric and pneumatic cables



MCLred

Reducing sleeve female/female, Cylindrical - steel



HK

Manual locking clamp, Manual locking clamp LWH



LVT

Miniature motorised actuator 2A, 2 amperes



VMS

Stainless steel knurled thumb screw, Knurled



FB_ECO

Eco. range steel bevel gear, 4:1



PSG125


Spur gear - precision range, Case hardened



LACT_SS

Adjustable Stainless steel cam lever, Male

Complementary products



BIMSS

Indexing plunger mini, miniature - Stainless steel



PPD

Indexing plunger for sheets, For sheet metal



PPF

Indexing plunger with flange, with drilled flange



DIV

Locking bolt, With grip - Steel