


Single or two part assembly

BAG1ss BAG2ss


- Solid fixing onto any type of shaft
- Do not separate the two pieces
- Materials:
 - Clamp + screw: stainless steel
 - Screw: steel alloy
- 2-part clamps offer a 20% stronger fixing
- Dimensions $\varnothing D$ and L are given as an indication only and are subject to change



stainless steel



Typical application



DISCOUNTS

Qty	1+	5+	10+	25+	50+
Disc	List	-6%	-12%	-18%	On request

Part number		$\varnothing A$	$\varnothing D$	L	Screw	Stock*	Stock*	Price each 1 to 4	
1 part	2 parts					1 part	2 parts	1 part	2 parts
BAG1-004/SS	BAG2-004/SS	4	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-005/SS	BAG2-005/SS	5	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-006/SS	BAG2-006/SS	6	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-008/SS	BAG2-008/SS	8	18	9	M3 x 8	✓	✓	9,11 €	10,67 €
BAG1-010/SS	BAG2-010/SS	10	24	9	M3 x 10	✓	✓	11,27 €	13,31 €
BAG1-012/SS	BAG2-012/SS	12	28	11	M4 x 12	✓	✓	11,64 €	13,81 €
BAG1-015/SS	BAG2-015/SS	15	34	13	M5 x 16	✓	✓	13,93 €	16,92 €
BAG1-016/SS	BAG2-016/SS	16	34	13	M5 x 16	✓	✓	13,93 €	16,92 €
BAG1-018/SS	BAG2-018/SS	18	36	13	M5 x 16	✓	✓	15,92 €	19,01 €
BAG1-020/SS	BAG2-020/SS	20	40	15	M6 x 16	✓	✓	19,40 €	20,24 €
BAG1-025/SS	BAG2-025/SS	25	45	15	M6 x 16	✓	✓	21,44 €	23,01 €
BAG1-030/SS	BAG2-030/SS	30	54	15	M6 x 18	✓	✓	24,76 €	27,59 €
BAG1-040/SS	BAG2-040/SS	40	60	15	M6 x 18	✓	✓	30,93 €	38,38 €
BAG1-050/SS	BAG2-050/SS	50	78	19	M8 x 25	✓	✓	58,29 €	84,96 €
BAG1-055/SS	BAG2-055/SS	55	90	16	M8 x 20	-	-	84,02 €	88,99 €
BAG1-060/SS	BAG2-060/SS	60	100	16	M8 x 20	-	✓	96,82 €	101,91 €
BAG1-070/SS	BAG2-070/SS	70	110	20	M10 x 25	-	-	107,85 €	113,61 €
BAG1-075/SS	BAG2-075/SS	75	125	20	M10 x 25	-	-	138,32 €	144,27 €
BAG1-080/SS	BAG2-080/SS	80	125	20	M10 x 25	-	-	131,65 €	137,52 €

*Depending on availability - Dimensions in mm


Our other products



BOX-TOR-MAX
Box set of Nitrile O-rings in nitrile, 2.90 x 1.78mm to 82.14 x 3.53



DHX
Dowel pin internal thread, Extractable DIN 7979D



AC
Strike for toggle latch, 15mm



SVG
Adjustable latch clamp with strike plate, Stroke from 118mm to 130,5mm



AWMP
Aluminium shaft for linear guide, Aluminium



UCFL
Cast iron flanged bearing, Cast iron




DFG
Flat suction cup, nitrile



SHTC
Drylin® Linear table, Maintenance free



H0
Crossed helical gear crossed axis at 90°, Steel 20NCD2



B
Steel bevel gear, 1:1



PRF-SRA
Lock for aluminium profile, Lock



H3
Crossed helical gear crossed axis at 90°, Machined plastic (delrin)

Complementary products



BAG
Steel Clamping collar, Steel



BAGSS
Stainless steel Clamping collar, Stainless steel



BAG-MISS
Split shaft collar with clamp lever, Stainless steel



BAP
Plastic clamping collar, Ø10 - Ø20