


Single or two part assembly

BAG1ss BAG2ss


- Solid fixing onto any type of shaft
- Do not separate the two pieces
- Materials:
Clamp + screw: stainless steel
Screw: steel alloy
- 2-part clamps offer a 20% stronger fixing
- Dimensions $\varnothing D$ and L are given as an indication only and are subject to change



stainless steel



Typical application



DISCOUNTS

Qty	1+	5+	10+	25+	50+
Disc	List	-6%	-12%	-18%	On request

Part number		$\varnothing A$	$\varnothing D$	L	Screw	Stock*	Stock*	Price each 1 to 4	
1 part	2 parts					1 part	2 parts	1 part	2 parts
BAG1-004/SS	BAG2-004/SS	4	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-005/SS	BAG2-005/SS	5	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-006/SS	BAG2-006/SS	6	16	9	M3 x 8	✓	✓	8,19 €	10,47 €
BAG1-008/SS	BAG2-008/SS	8	18	9	M3 x 8	✓	✓	9,11 €	10,67 €
BAG1-010/SS	BAG2-010/SS	10	24	9	M3 x 10	✓	✓	11,27 €	13,31 €
BAG1-012/SS	BAG2-012/SS	12	28	11	M4 x 12	✓	✓	11,64 €	13,81 €
BAG1-015/SS	BAG2-015/SS	15	34	13	M5 x 16	✓	✓	13,93 €	16,92 €
BAG1-016/SS	BAG2-016/SS	16	34	13	M5 x 16	✓	✓	13,93 €	16,92 €
BAG1-018/SS	BAG2-018/SS	18	36	13	M5 x 16	✓	✓	15,92 €	19,01 €
BAG1-020/SS	BAG2-020/SS	20	40	15	M6 x 16	✓	✓	19,40 €	20,24 €
BAG1-025/SS	BAG2-025/SS	25	45	15	M6 x 16	✓	✓	21,44 €	23,01 €
BAG1-030/SS	BAG2-030/SS	30	54	15	M6 x 18	✓	✓	24,76 €	27,59 €
BAG1-040/SS	BAG2-040/SS	40	60	15	M6 x 18	✓	✓	30,93 €	38,38 €
BAG1-050/SS	BAG2-050/SS	50	78	19	M8 x 25	✓	✓	58,29 €	84,96 €
BAG1-055/SS	BAG2-055/SS	55	90	16	M8 x 20	-	-	84,02 €	88,99 €
BAG1-060/SS	BAG2-060/SS	60	100	16	M8 x 20	-	✓	96,82 €	101,91 €
BAG1-070/SS	BAG2-070/SS	70	110	20	M10 x 25	-	-	107,85 €	113,61 €
BAG1-075/SS	BAG2-075/SS	75	125	20	M10 x 25	-	-	138,32 €	144,27 €
BAG1-080/SS	BAG2-080/SS	80	125	20	M10 x 25	-	-	131,65 €	137,52 €

*Depending on availability - Dimensions in mm

Our other products



PCS6ECO
Chain sprocket - steel,
6mm (DIN 04-1)



OP2
Mechanical digital
position indicator, 3
numbers



CHML40
Worm and wheel gear
reducer, up to 57 Nm
- Integrated torque
limiter



VMS
Stainless steel knurled
thumb screw, Knurled



DIV
Locking bolt, With grip
- Steel



NCT
Square tube
connector, Fixed
angle



PRF4590
Standard aluminium
profile, 45 x 90 mm



PCS37K
Chain sprocket with
hardened teeth,
9.525mm (DIN06B-1)



SSDB
Stainless steel bevel
gear, 2:1



GPBSS
Threaded spherical
knob, Aluminium



LSAG
Precision linear rotary
ball spline, Rail - from
514 N to 15386 N



UTKswcr
Utilitrak® 3 wheels
carriage, Steel roller
carriage

Complementary products



BAGSS
Stainless steel
Clamping collar,
Stainless steel



BAG
Steel Clamping collar,
Steel