



Right angled gearbox, dual output shafts



Torque up to 128Nm

BLHM70

- Input and two outputs have a reversed sens of direction
- Ratios of 1:1 to 2:1
- Output backlash $\approx 1^\circ$
- Max. speed: 4,000 rpm
- Materials: casing: anodised aluminium
input: hardened steel,
output: hardened steel
- Weight: 8.76 kg

Options

- Can be modified to your specifications



Output torque Nm (Nm values given as a guide only)

Ratios	1:1	2:1
3000	43	26
2000	47	30
INPUT 1000	51	34
SPEED 500	64	38
(rpm) 100	85	51
50	94	60
10	128	77

Innovative !
Outputs rotate in
different directions

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-15%	On request

Part number	Ratio	Efficiency at 1000 rpm	Max. input speed (rpm)	Max. output speed (rpm)	Module	Price each
BLHM70-1	1:1	88%	3000	3000	4,0	On request
BLHM70-2	2:1	88%	3000	1500	2,5	On request

Dimensions in mm

Our other products



TSRTC

Stem support for
caster, For swivel
caster with central
hole



SDG_SS

Universal adjustable
guide support
bracket, Stainless
steel



BOX-WM

Box set of washer -
DIN125, Box set of
steel washers



EMS

Stainless steel knurled
thumb nut, Knurled
steel



BPHF

Ball transfer unit push
fit, Heavy



VTLF

3 lobed handle,
Polyamide - Brass



TIFbout

Threaded stud -
DIN976A, Steel



WSS

Symmetrical S shaped
hook, Steel



PRF45_GOU

Chute profile,
Accessories



PVL

Small lobed handle,
Polyamide



PRF-SCREEN-4

Screen support,
Support with 4 axes of
rotation



PRF_CLIP_22

Cable clip for
aluminium profile, For
electric and
pneumatic cables

Complementary products



BLH70

Right angled gearbox,
from 26 to 128 Nm



BLHT70

Right angled gearbox,
from 26 to 128 Nm