

Flush fitting ball transfer unit with flange

BPHF

For heavy loads

- Carrying ball for handling solid body
- For heavy loads
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:

BPHF:galvanised steel body and chromed steel ball

BPHF/AS:galvanised steel body and 420 stainless steel balls

BPHF/SS:body, components and balls- 420 stainless steels




Accessoires

- BPHFCLIP mounting clip

Advantages

- Good resistance to shocks
- Optional clips compensate for irregularities in seat bore diameter



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-10%	-15%	-20%	On request

Part N°	Ødwb ball	ØA	B	C	ØD	E	Carrying capacity (kg)	Weight (g)	Price each 1 to 5
Steel body, steel balls									
BPHF15-24	15	24	9,5	4,0	31	21,0	60	0,059	4,96 €
BPHF22-36	22	36	9,8	3,8	45	30,5	180	0,189	9,68 €
BPHF30-45	30	45	13,8	5,8	55	36,8	350	0,360	15,32 €
BPHF45-62	45	62	19,0	9,0	75	53,5	600	1,010	49,56 €
Steel body, stainless steel balls									
BPHF15-24/AS	15	24	9,5	4,0	31	21,0	50	0,059	6,18 €
BPHF22-36/AS	22	36	9,8	3,8	45	30,5	180	0,188	10,72 €
BPHF30-45/AS	30	45	13,8	5,8	55	36,8	350	0,357	18,79 €
BPHF45-62/AS	45	62	19,0	9,0	75	53,5	600	1,000	65,24 €
Stainless steel body, stainless steel balls									
BPHF15-24/SS	15	24	9,5	4,0	31	21,0	40	0,058	16,90 €
BPHF22-36/SS	22	36	9,8	3,8	45	30,5	126	0,188	40,04 €
BPHF30-45/SS	30	45	13,8	5,8	55	36,8	220	0,357	53,68 €
BPHF45-62/SS	45	62	19,0	9,0	75	53,5	350	1,020	132,12 €

All dimensions in mm

Our other products



CLM

Male clevis end,
Stainless steel short



PRF_CHA

Hinge for aluminium
profile, Surface
mounting hinge



MSP23

Masterplate®
glueable insert Ø23,
Cylindrical Ø23 with
threaded s...



PRF19_E

Bracket for aluminium
profile, PRF19 to
PRF45



EFTC

Fixing support,
Stainless steel



PRF1932

Standard aluminium
profile, 19 x 32 mm



RDE-W

Sealing washer
Hygienic Usit®,
Stainless steel - White
EPDM




PRF_ER

Joining bar for
aluminium profile,
joint bar



CHAE4080PA

Symmetrical decorative
screwed hinge,
Polyamide



CFC

Spring loaded position
switch, Electric
contact



CABtool

Fitting cable tools,
Crimping tools



J51

Spur gear coaxial
gearbox, from 0.13 to
0.49 Nm - In-line

Complementary products



BPHF

Ball transfer unit push
fit, Heavy



BPHF

Ball transfer unit push
fit, Heavy



BPPE

Ball transfer unit push
fit, Light



BPLE

Ball transfer unit push
fit, Light