



# Spring loaded ball transfer unit

For heavy loads


**BPHRF**

- **Ball transfer unit with solid body**
- For heavy loads
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:  
Galvanised steel body and chromed steel balls



## Advantages

- Good resistance to shocks



## DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-10%	-15%	-20%	On request

Part N°	Ødw ball	ØA	B	ØC	D	E	Carrying capacity (kg)	Load at max		Price each 1 to 5
								Deflection	deflection	
BPHRF22-39	22	39,0	58,0	50	14,0	53,5	70	4,5	90	66,18 €
BPHRF30-48	30	48,5	70,0	62	17,5	63,0	135	7,0	170	104,32 €
BPHRF45-66	45	66,5	100,5	85	25,5	90,0	230	10,5	290	136,41 €

All dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

Fax

cial2@hpceurope.com

**HPC**

SUPPLEMENT 2019

263

## Our other products



Locking pin with interlocking safety latch, with interlocking safety...



Cable-carrier chain for aluminium profile, Supplied in metre lengths



Worm and wheel set, Hardened steel



Stainless/Polymer pillow block bearing, Cast iron - Split pillow




301 Stainless steel ball pin, Stainless steel



Worm and wheel gear reducer, up to 164 Nm



90° ball and socket joints DIN71802, Steel



Aluminium profile anodising polisher, Polishing block



HTD Heavy duty timing pulley, HTD8



Stainless steel/Polymer flanged



Hinge without pin, Plastic hinge



HEAVY DUTY spur gear, Steel 35NCD6

## Complementary products



Ball transfer unit housed spring loaded, High