



# Spring loaded ball transfer unit

For heavy loads


BPHRF

- Ball transfer unit with solid body
- For heavy loads
- Machined bodies and covers
- Lubricated for life
- Orientation: horizontal with ball upwards
- Unique drainage hole
- Max. speed: 1.5m/s
- Working temperature range: -30 to +100°C
- Materials:  
Galvanised steel body and chromed steel balls



## Advantages

- Good resistance to shocks



## DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-10%	-15%	-20%	On request

Part N°	Ødw ball	ØA	B	ØC	D	E	Carrying capacity (kg)	Load at max		Price each 1 to 5
								Deflection	deflection	
BPHRF22-39	22	39,0	58,0	50	14,0	53,5	70	4,5	90	66,18 €
BPHRF30-48	30	48,5	70,0	62	17,5	63,0	135	7,0	170	104,32 €
BPHRF45-66	45	66,5	100,5	85	25,5	90,0	230	10,5	290	136,41 €

All dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

Fax

cial2@hpceurope.com

**HPC**

SUPPLEMENT 2019

263

## Our other products



M2

Worm and wheel set,  
Machined plastic  
(delrin)



BLHT20

Right angled gearbox,  
from 0.66 to 1.77 Nm



BLM

Spring loaded plunger  
with ball tip, Plastic  
body




ACLERP

Roller block for  
aluminium profile,  
With guide rail



DOMI30

Connecting kits, ZX  
linking kit



ACLBTS

Closing system for  
aluminium profile, 90°  
bracket for spherical  
end...



PTRSS

Idle chain sprocket,  
For hostile  
environments



CHAFR-MINI

Miniature friction  
hinge, Friction



H2

Crossed helical gear  
crossed axis at 90°,  
Steel 20NCD2



CABPVC

PVC covered  
galvanised steel  
cable, Galvanised  
steel with



UGH32

H Type Guide units,  
For Ø32 actuators



BOX-TOR-H

Box set of Nitrile O-  
rings in nitrile, 3.00 x  
2.00mm to 45.20 x  
4.00

## Complementary products



BPHR

Ball transfer unit  
housed spring loaded,  
High